


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19  
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

PROD 4092 CODE	LOC DF	DIST SO	P ✓	F ✓	REVISIONS				DATE	APPD
					ZONE	LTR	DESCRIPTION			
					B		REV & REDRAWN PER DF-2202	CT	11/29/89	San Gaby



1. MARKED PER MIL-STD-130.
  2. TO MATE WITH AMP LGH-1 RECEPTACLE WITH 1.00 BARREL DEPTH.
  3. OPERATING VOLTAGE: 20 KVDC AT 0 TO 70,000 FEET, -55° TO 125°C.
- △ TOLERANCE: UP TO 24" [609.6] = ±.12 [±3.0]  
24" [609.6] & UP = 1%.

DO NOT SCALE PRINT.  
UNLESS SPECIFIED  
DIMENSIONS IN INCHES [mm]  
TOLERANCES ON:  
2 PLC DEC ±.02 [0.51]  
3 PLC DEC ±  
ANGLES ±

MATERIAL

SEE CALLOUTS

FINISH

DR 11-8-89  
C.C. THOMAS

CHK -

APPD *San Gaby* 11/29/89APPD *San Gaby* 11/29/89

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

**AMP** AMP INCORPORATED  
Harrisburg, Pa. 17105

NAME

LEAD ASS'Y, LGH-SPCL END W/J1-21 BOOT

SIZE

C

SCALE

CAGE CODE  
00779

DRAWING NO

863550

SHEET

1 OF 1

METRIC

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[863550-1](#)