

Contact Part No.		Contact Size	Insertion / Removal Tool		Crimping	
			Insertion	Withdraw	Crimp Tool	Positioner
Military	TE	AWG	M81969 Slash No.	M81969 Slash No. (Wired)	M22520 Slash No.	M22520 Slash No.
M29600 Contacts						
M29600/23 Socket Contacts (For AS29600 Connectors)						
/23-606	12343-23	23/22	/16-04	/16-04	/2-01	/2-16
/23-607	12343-20	20	/16-01	/16-01	/2-01	/2-17
/23-608	12343-16	16	/16-02	/16-02	/2-01	/2-18
M29600/23 Pin Contacts (For AS29600 Connectors)						
/24-610	12341-23	23	/16-04	/16-04	/2-01	/2-13
/24-611	12341-20	20	/16-01	/16-01	/2-01	/2-14
/24-612	12341-16	16	/16-02	/16-02	/2-01	/2-15
M39029 Contacts						
M39029/1 Pin Contacts (For AS81714 Series I Terminal System)						
/1-100	2560-214-1631	16	/14-10	/14-10	/2-01	/2-11
/1-101	2560-215-1631L	16/20	/14-10	/14-10	/1-01, /2-01	/1-02, /2-11
/1-102	2560-216-1431	14/16	/14-03	/14-03	/1-01	/1-02
/1-103	2560-217-1231	12	/14-04	/14-04	/1-01	/1-02
/1-507	2560-218-2031	20/22D	/14-01, /1-04, /8-01, /8-02	/14-01, /1-04, /8-01, /8-02	/1-01	/2-32
M39029/4 Pin Contacts (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)						
/4-110	0641-1-2031L	20	/14-11	/14-11	/1-01	/1-02
/4-111	0641-2-1631L	16	/14-03, /8-207	/14-03, /8-208	/7-01	/1-02, /7-03
/4-112	109026-31	16/20	/14-03, /8-207	/14-03, /8-208	/1-01, /7-01	/1-02, /7-03
/4-113	0641-3-1231L	12	/14-04, /14-04	/14-04, /8-210	/1-01	/1-02
/4-114	109028-31L	12	/14-04, /8-209	/14-04, /8-210	/1-01	/1-03
M39029/5 Socket Contacts (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)						
/5-115	100503L	20	/14-11, /8-07	/14-11, /8-06	/1-01, /2-01, /7-01	/1-02, /2-02, /7-02
/5-116	100504L	16	/14-03, M91659/8-07	/14-03, /8-08	/1-01, /7-01	/1-02, /7-03
/5-117	109027	16/20	/14-03, /8-207	/14-03, /8-208	/1-01	/1-02, /7-03
/5-118	100505L	12	/14-04, /8-209	/14-04, /8-210	/1-01	/1-02
/5-119	109029	12/16	/14-04, /8-209	/14-04, /8-210	/1-01	/1-02
M39029/10 Socket Contacts — Thermocouples (For MIL-DTL-26482 Series II, -83723 Series III, -83733, and AS81703 Connectors)						
/10-521	7362-255-1601	16	/14-03	/14-03	/1-01, /7-01	/1-02, /7-03
/10-522	7362-226-1601	16	/14-03	/14-04	/1-01, /7-01	/1-02, /7-03
M39029/11 Pin Contacts (For AS81659 Series II Connectors)						
/11-144	2560-212-2231	22	/1-01	/1-01	/2-01	/2-23
/11-145	2560-212-2031	20	/1-02	/1-02	/2-01, /7-01	/2-08, /7-02
M39029/12 Socket Contacts (For AS81659 Series II Connectors)						
/12-148	2562-209-2231	22	/1-01	/1-01	/2-01	/2-23
/12-149	2562-209-2031	20	/1-02	/1-02	/2-01, /7-01	/2-08, /7-02
M39029/16 Socket Contacts (For AS81511 Series IV Connectors)						
/16-166	81542-238	23/28	/16-04	/16-04	/2-01	/2-13
/16-167	81542-23	23/22	/16-04	/16-04	/2-01	/2-13
/16-168	81542-20	20	/16-01	/16-01	/2-01	/2-14
/16-169	81542-16	16	/16-02	/16-02	/2-01	/2-15
/16-170	81542-12	12	/16-03	/16-03	/1-01	/1-09
M39029/17 Socket Contacts (For AS81511 Series III Connectors)						
/17-171	81543-238	23	/16-04	/16-04	/2-01	/2-16
/17-172	81543-23	23	/16-04	/16-04	/2-01	/2-16
/17-173	81543-20L	20	/16-01	/16-01	/2-01	/2-17
/17-174	81543-16	16	/16-02	/16-02	/2-01	/2-18
/17-175	81543-12	12	/16-03	/16-03	/1-01	/2-10

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L. Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility. For wire size, a double number indicates Mating End/Crimp End.

For More Information

TE Technical Support Center

North America	+1 800 522 6752
Asia Pacific	+86 0 400 820 6015
Austria	+43 1 905 601 228
Baltic Regions	+46 8 5072 5000
Benelux	+31 73 6246 999
Czech Republic	+420 800 701 462
France	+33 1 34 20 86 86
Germany	+49 6251 133 1999
Hungary	+36 809 874 04
Italy	+39 011 401 2632
Nordic	+46 8 5072 5000
Poland	+48 800 702 309
Russia	+7495 790 790 2
Spain/Portugal	+34 93 2910366
Switzerland	+41 52 633 66 26
United Kingdom	+44 800 267 666

Follow us on Twitter for all the latest product news @TEConnectivity, and on Facebook, TEConnectivity.

www.te.com/ADM

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773735-3 ADM/RRD 1M 12/2014

DEUTSCH, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.



QUICK REFERENCE GUIDE

High Performance

- Achieve enhanced durability – 1500 cycles (insertion/withdrawals)
- Terminate to aluminum or standard wires

More Compatibility

- Use with full range of mil-spec connectors
- Meet ASE/EN requirements

Contact Part No.		Contact Size	Insertion / Removal Tool		Crimping	
			Insertion	Withdraw	Crimp Tool	Positioner
Military	TE	AWG	M81969 Slash No.	M81969 Slash No. (Wired)	M22520 Slash No.	M22520 Slash No.
M39029 Contacts						
M39029/18 Pin Contacts (For AS81511 Series III and IV Connectors)						
/18-176	81541-238	23	/16-04	/16-04	/2-01	/2-13
/18-177	81541-23	23	/16-04	/16-04	/2-01	/2-13
/18-178	81541-20	20	/16-01	/16-01	/2-01, /7-01	/2-14, /7-02
/18-179	81541-16	16	/16-02	/16-02	/2-01, /7-01	/2-15, /7-03
/18-180	81541-12	12	/16-03	/16-03	/1-01	/1-09
M39029/22 Socket Contacts (For AS81714 Series II Terminal System and AS81511 Series III and IV Connectors)						
/22-191	CTS-S22/22	22	—	—	/7-01	/7-11
/22-192	CTS-S20/20	20	/14-10	—	/7-01	/7-12
/22-193	CTS-S16/16	16	/14-03	—	/7-01	/7-13
/22-605	CTS-S12/12	12	/8-10, /16-03	—	/1-01	—
M39029/28 Pin Contacts • Coax (For MIL-DTL-38999 Series I, II, III, and IV Connectors)						
/28-211	6162-233-1277	—	/8-09	—	—	—
/28-409	6162-234-1277	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/28-414	6162-239-1277	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
M39029/29 Pin Contacts (For AS50151, MS5450, and MIL-DTL-83723 Series II Connectors)						
/29-212	0660-206-1631L	16	/14-03	/14-03	/1-01, /7-01	/1-02, /7-03
/29-213	0660-206-1282	12	/14-04	/14-04	M22750/1-01	/1-02
/29-214	0660-206-0882 (Silver)	8	—	/29-02	/23-01	—
/29-215	0660-206-0482 (Silver)	4	—	/29-03	/23-01	—
/29-216	0660-206-0082 (Silver)	0	—	/29-04	/23-01	—
M39029/30 Socket Contacts (For AS50151, MS5450, and MIL-DTL-83723 Series II Connectors)						
/30-217	0662-212-1631L 182-0400-16	16S/16	/14-03	/14-03	/1-01, /7-01	/1-02, /7-03
/30-218	0662-207-1631L	16	/14-03	/14-03	/1-01, /7-01	/1-02, /7-03
/30-219	0662-207-1282 (Silver)	12	/14-04	/14-04	/1-01	/1-02
/30-220	0662-207-0882 (Silver)	8	—	/29-02	/23-01	—
/30-221	0662-207-0482 (Silver)	4	—	/29-03	/23-02	—
/30-222	0662-207-0082 (Silver)	0	—	/29-04	/23-03	—
M39029/31 Pin Contacts (For MIL-DTL-26482 Series I and -26500 Connectors)						
/31-228	4160-203-1631L	16	/14-03, /17-04	/19-01	/1-01	—
/31-229	4160-204-1631L	16	/14-03, /17-04	/19-01	/1-01, /7-01	/1-02BLUE, /7-03
/31-240	0004-058-100L	20	/14-10, /17-03	/19-06	/1-01, /2-01, /7-01	/1-02, /2-02, /7-02
/31-627	4160-202-2031L	20	/14-10, /17-03	/19-06	/1-01, /2-01, /7-01	/1-02, /2-02, /7-02
M39029/32 Socket Contacts (For MIL-DTL-26482 Series I and -26500 Connectors)						
/32-247	4162-201-1631L	16	/14-03, /14-04	/19-01	/1-01, /7-01	/1-02, /7-03
/32-248	4162-202-1631L	16	/14-03, /14-04	/19-01	/1-01, /7-01	/1-02, /7-03
/32-259	0007-008-100L	20	/14-10, /17-03	/19-06	/1-01, /2-01, /7-01	/1-02, /2-02, /7-02
/32-260	4109-207-2000L	20	/14-10, /17-03	/19-06	/1-01, /2-01, /7-01	/1-02, /2-02, /7-02
M39029/56 Socket Contacts (For MIL-DTL-38999 Series I, III, and IV and EN3645 Connectors)						
/56-348	38943-22L 724-0007-22 EN3155-009F2222	22/22D	/14-01, /8-02	/14-01, /8-02	/2-01, /7-01	/2-07, /7-05
/56-351	38943-20L 724-0007-20 EN3155-009F2020	20	/14-10, /8-05	/14-10, /8-06	/2-01, /7-01, /1-01	/2-10, /7-08, /1-04
/56-352	38943-16L 724-0007-16 EN3155-009F1616	16	/14-03, /8-07	/14-03, /8-08	/1-01, /7-01	/1-04, /7-04
/56-353	38943-12L 724-0007-12 EN3155-009F1212	12	/14-04, /8-09	/14-04, /8-10	/1-01	/1-04

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L. Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility. For wire size, a double number indicates Mating End/Crimp End.

Contact Part No.		Contact Size	Insertion / Removal Tool		Crimping	
			Insertion	Withdraw	Crimp Tool	Positioner
Military	TE	AWG	M81969 Slash No.	M81969 Slash No. (Wired)	M22520 Slash No.	M22520 Slash No.
M39029 Contacts						
M39029/57 Socket Contacts (For MIL-DTL-38999 Series II, -24308, -83733, -55302, and EN4165 Connectors)						
/57-354	38946-22L 724-0003-22EN3155-003F2222	22/22D	/14-01, /8-01	/14-01, /8-02	/2-01, /7-01	/2-06, /7-06
/57-357	38946-20L 724-0003-20 EN3155-003F2020	20	/14-02, /8-05	/14-02, /8-08	/2-01, /7-01, /1-01	/2-10, /7-08, /1-04
/57-358	38946-16L 724-0003-16 EN3155-003F1616	16	/14-03, /8-07	/14-03, /8-08	/1-01, /7-01	/1-04, /7-04
/57-359	38946-12 724-0003-12 EN3155-003F1212	12	/14-04, /8-09	/14-04, /8-10	/1-01	/1-04
M39029/58 Pin Contacts (For MIL-DTL-38999 Series I, II, III, and IV, -24308, -83733, -55302, EN3645, and EN4165 Connectors)						
/58-360	38941-22L 724-0001-22 EN3155-008M2222	22/22D	/14-01, /8-01	/14-01, /8-02	/2-01, /7-01	/2-09, /7-07
/58-363	38941-20L 724-0001-22 EN3155-008M2020	20	/14-10, /8-05	/14-10, /8-06	/2-01, /7-01, /1-01	/2-10, /7-08, /1-04
/58-364	38941-16L 724-0001-16 EN3155-008M1616	16	/14-03, /8-07	/14-03, /8-08	/1-01, /7-01	/1-04, /7-04
/58-365	38941-12L 724-0001-12 EN3155-008M1212	12	/14-04, /8-09	/14-04, /8-10	/1-01	/1-04
M39029/63 Socket Contacts (For MIL-DTL-24308 Connectors)						
/63-368	2562-201-2031L	20	/39-01, /1-02	/39-01, /1-02	/2-01	/2-08
M39029/64 Pin Contacts (For MIL-DTL-24308 Connectors)						
/64-369	2560-201-2031L	20	/39-01, /1-02	/39-01, /1-02	/2-01	/2-08
M39029/75 Socket Contacts • Coax (For MIL-DTL-38999 Series I, III, and IV Connectors)						
/75-416	6162-217-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-417	6162-218-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-418	6162-219-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-419	6162-220-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-421	6162-222-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-422	6162-223-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
/75-423	6162-224-1277 (Au/Ni)	—	/8-09, /14-04	/8-10, /14-04	/2-01, /31-01	/2-34, /31-02
M39029/76 Pin Contacts • Coax (For MIL-DTL-38999 Series I, II, III, and IV and -24308 Connectors)						
/76-424	6162-229-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, /14-03	/2-01, /4-01	/2-35, /4-01
/76-425	6162-230-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, /14-03	/2-01, /4-01	/2-35, /4-01
/76-426	6162-231-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, /14-03	/2-01, /4-01	/2-35, /4-01
/76-427	6162-232-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, /14-03	/2-01, /4-01	/2-35, /4-01
M39029/77 Socket Contacts • Coax (For MIL-DTL-38999 Series I, III, and IV Connectors)						
/77-428	6162-213-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/77-429	6162-214-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/77-430	6162-215-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/77-431	6162-216-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
M39029/78 Socket Contacts • Coax (For MIL-DTL-38999 Series II and -24308 Connectors)						
/78-432	6162-253-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/78-433	6162-254-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/78-434	6162-255-1677 (Au/Ni)	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02
/78-435	6162-256-1677	—	/8-07, /14-03	/8-08, 14-03	/2-01, /4-01	/2-35, /4-02

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L. Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility. For wire size, a double number indicates Mating End/Crimp End.

Contact Part No.		Contact Size	Insertion / Removal Tool		Crimping	
			Insertion	Withdraw	Crimp Tool	Positioner
Military	TE	AWG	M81969 Slash No.	M81969 Slash No. (Wired)	M22520 Slash No.	M22520 Slash No.
M39029 Contacts						
M39029/83 Pin Contacts (For MIL-DTL-28840 Connectors)						
/83-450	2560-221-2031L	20/22	/33-01	/34-01	/34-01	/34-02
/83-451	2560-222-2031L	20/28	/33-01	/34-01	/34-01	/34-02
/83-508	2560-220-2031L	20	/33-01	/34-01	/34-01	/34-02
M39029/84 Socket Contacts (For MIL-DTL-28840 Connectors)						
/84-452	2562-214-2031L	20/22	/33-01	/34-01	/34-01	/34-02
/84-453	2562-215-2031L	20/28	/33-01	/34-01	/34-01	/34-02
/84-509	2562-213-2031L	20	/33-01	/34-01	/34-01	/34-02
M39029/90 Pin Contacts • Twinax (For MIL-DTL-38999 Series III and IV Connectors)						
/90-529	6162-283-0877	—	/14-12	/14-12	/2-01, /5-01	/2-37, /5-105
M39029/91 Socket Contacts • Twinax (For MIL-DTL-38999 Series III and IV Connectors)						
/91-530	6162-284-0877	—	/14-12	/14-12	/2-01, /5-01	/2-37, /5-105
M39029/101 Socket Contacts (For MIL-DTL-12883 Sockets and MIL-PRF-Relays)						
/101-553	1662-213-2031L	20	/16-01	/16-01	/7-01, /1-01	/7-12
/101-554	1662-213-1631L	16	/16-02	/16-02	/7-01	/7-13
M39029/102 Pin Contacts • Coax (For MIL-DTL-38999 Series III and IV Connectors)						
/102-558	6162-324-1231	—	/8-09, /14-04	/8-10, /14-04	/5-01	—
M39029/103 Socket Contacts • Coax (For MIL-DTL-38999 Series III and IV Connectors)						
/103-559	6162-325-1231	—	/8-09, /14-04	/8-10, /14-04	/5-01	—
M39029/106 Socket Contacts (For MIL-DTL-38999 Series III and IV, AS29600 Series A, and EN3645 Connectors)						
/106-614	12333-22 182-0447-22	22/22D	/14-01, /8-01	/14-01, /8-02	/2-01, /7-07	/2-07, /7-05
/106-615	12333-20 182-0447-20	20	/14-10, /8-07	/14-10, /8-06	/1-01, /2-01, /7-01	/1-04, /2-10, /7-08
/106-616	12333-16 182-0447-16	16	/14-03, /8-07	/14-03, /8-08	/1-01, /7-01	/1-04, /7-04
/106-617	12333-12 182-0447-12	12	/14-04, /8-09	/14-04, /8-10	/7-01	/1-04
M39029/107 Pin Contacts (For MIL-DTL-38999 Series III and IV, AS29600 Series A, and EN3645 Connectors)						
/107-620	12331-22 182-0441-22	22/22D	/14-01, /8-01	/14-01, /8-02	/2-01, /7-01	/2-07, /7-05
/107-621	12331-20 182-0441-20	20	/14-10, /8-05	/14-10, 8-06	/1-01, /2-01, /7-01	/1-04, /2-10, /7-08
/107-622	12331-16 182-0441-16	16	/14-03, /8-07	/14-03, /8-08	/1-01, /7-01	/1-04, /7-04
/107-623	12331-12 182-0441-12	12	/14-04, /8-09	/14-03, /8-10	/1-01	/1-04

Part numbers ending in trailing L are available with localized gold plating, according to ASTM B 488, Type II, Code C: 50 micro-inches over nickel underplating. For full plating, remove the trailing L. Italicized part numbers are for the TE's Evreux facility. All others are for TE's Oceanside facility. For wire size, a double number indicates Mating End/Crimp End.

TE Components . . . TE Technology . . . TE Know-how . . .
AMP | Agastat | CII | Hartman | Kilovac | Microdot | Nanonics | Raychem | Rochester | DEUTSCH

Get your product to market faster with a smarter, better solution.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[M39029/58-363](#) [M39029/4-112](#) [M39029/57-357](#) [M39029/28-409](#) [M39029/76-424](#) [M39029/16-168](#) [M39029/5-119](#)
[M39029/32-247](#) [M39029/17-172](#)