



Harnessing > Heat Shrink Components > End Caps



Wall Type: **Dual**
Material Code: **3**
Sealant: **Yes**
Material Systems Code: **10**
Adhesive Pre-Coat: **Yes**

Features

Product Type Features

Size Code	94
Wall Type	Dual

Body Features

Color	Black
Material	Crosslinked Polyolefin
Shrink Ratio	2:1
Pliancy	Flexible
Lining Type	Adhesive
Material Code	3
Sealant	Yes
Material Systems Code	10
Adhesive Pre-Coat	Yes

Dimensions

Length	114 mm[4.5 in]
Recovered Inside Diameter (Max)	38.1 mm[1.5 in]
Recovered Wall Thickness (Nominal)	3.05 mm[.12 in]
Expanded Inside Diameter (Min)	83.8 mm[3.3 in]
Wall Thickness	Medium

Usage Conditions

--



Flammability	Flame-Retardant
Resistance Protection	Suitable for occasional exposure to fluids
Resistance Properties	Immersion Protection
Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]

Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	/86 Precoat
Molded Part Shape Code	101A
Adhesive Type	High Performance Pre-Coat Adhesive
Adhesive Options	/86 Precoat

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	欧洲化学品管理局最新发布的SvHCs候选清单: 2019年1月（197） SvHCs候选清单的声明更新至: 2019年1月（197）
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.




Compatible Parts



TE Part # CJ2087-000

[HL2010E-KIT-120V](#)

Customers Also Bought




TE Part #602513-000

[462A023-3/86-0](#)



TE Part #F07461-000

[101A083-3/86-0](#)




TE Part #024285-000

[202G653-55-0](#)




TE Part #2-487938-4

[024 HOUSING FFC 50CL DR](#)




TE Part #725605-000

[301A034-3/86-0](#)




TE Part #446852-8

[3 ROW BOX PIN 240P R/A SEALED](#)



TE Part #148468-000

[462A034-3/86-0](#)



TE Part #868594-3

[LGH 4 DBL MLD END LEAD ASY](#)



TE Part #1-1617069-0

[DS9-1W=DS9 DIP SOLID STATE RELAY](#)



TE Part #YDTS26W23-55PAV001

[PLUG ASSY](#)

Documents

Product Drawings

[101A094-3/86-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-3](#)

English



Product Specifications

Product Specification

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[101A094-3/86-0](#)