



55A1811-24-9-9 Product Details

[Share](#) | [Print](#) | [Email](#)


55A1811-24-9-9

TE Internal Number: 333000-000

Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 24 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Cable Type = Spec 55 • Cable Style = Jacketed, Round-Braid Shielded <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Voltage Rating (VAC) = 600 <p>Dimensions:</p> <ul style="list-style-type: none"> • Conductor Outer Diameter (mm [in]) = 0.61 [0.024] • Shield (Screen) Diameter (mm [in]) = 1.57 [0.062] <p>Body Features:</p> <ul style="list-style-type: none"> • Wire Size (AWG/CM) = 24 AWG • Cable Jacket Color = White • Conductor Type = Tin-Plated Copper • Wire Color = White • Nominal Outside Diameter (mm [in]) = 1.98 [0.078] • Wire Diameter (mm [in]) = 1.14 [0.0448] <p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Conductors = 1 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • Government/Industry Qualification = No • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Range (°C) = -65 - +150 • Wire Size - Details = 24 AWG 0.24 mm², 0.00037 in², 19 x 36 AWG <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Airframe - Medium Weight <p>Packaging Features:</p> <ul style="list-style-type: none"> • Wire Source = United States <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A1811-24-9-9](#)