



Home > Products > Wire & Cable > Product Feature Selector > Product Details

44A1121-22-0/9-90-US Product Details

[Share](#) [Print](#) [Email](#)


44A1121-22-0/9-90-US

TE Internal Number: 383341-000

 Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

 Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 22 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Product Drawings: • CABLE, RADIATION-CROSSLINKED, POLYALKENE-INSULATED, ... (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Cable Type = Spec 44 • Cable Style = Jacketed, Round-Braid Shielded Electrical Characteristics: • Voltage Rating (VAC) = 600 Dimensions: • Conductor Outer Diameter (mm [in]) = 0.79 [0.031] • Shield (Screen) Diameter (mm [in]) = 2.95 [0.116] Body Features: • Wire Size (AWG/CM) = 22 AWG • Cable Jacket Color = White w/ Black Stripe • Conductor Type = Tin-Plated Copper • Wire Color = Black, White • Nominal Outside Diameter (mm [in]) = 3.35 [0.132] • Wire Diameter (mm [in]) = 1.19 [0.047] Configuration Features: • Number of Conductors = Twisted Pair	Industry Standards: • Government/Industry Qualification = No • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Converted to comply with RoHS directive Conditions for Usage: • Temperature Range (°C) = -65 – +150 • Wire Size - Details = 22 AWG 0.38 mm², 0.00059 in², 19 x 34 AWG Operation/Application: • Application = General Purpose - Lightweight Packaging Features: • Wire Source = United States Other: • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility
Plan](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[44A1121-22-0/9-90-US](#)