




[Home](#) > [Products](#) > [Wire & Cable](#) > [Product Feature Selector](#) > Product Details

44A0811-16-0 Product Details

[Share](#) [Print](#) [Email](#)


44A0811-16-0

TE Internal Number: 265099-000

 Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 44
- Wire Source = United Kingdom, United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 16 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Product Drawings: • WIRE, ELECTRIC, RADIATION-CROSSLINKED, POLYALKENE-IN... (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Related Products: • Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Cable Type = Spec 44 • Cable Style = Primary Electrical Characteristics: • Voltage Rating (VAC) = 600 Dimensions: • Conductor Outer Diameter (mm [in]) = 1.42 [0.056] Body Features: • Wire Size (AWG/CM) = 16 AWG • Conductor Type = Tin-Plated Copper • Wire Color = Black • Nominal Outside Diameter (mm [in]) = 2.26 [0.089] • Wire Diameter (mm [in]) = 2.26 [0.089] Configuration Features: • Number of Conductors = 1	Industry Standards: • Government/Industry Qualification = No • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Temperature Range (°C) = -65 - +150 • Wire Size - Details = 16 AWG 1.23 mm², 0.002 in², 19 x 29 AWG Operation/Application: • Application = Medium Weight Packaging Features: • Wire Source = United Kingdom, United States Other: • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[44A0811-16-0](#)