



55A1811-12-9-9CS2275 Product Details

[Share](#) | [Print](#) | [Email](#)


Spec 44, Spec 55 and Spec RCW Wire and Cable

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG/CM) = 12 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

55A1811-12-9-9CS2275

TE Internal Number: 839467-000

Active

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information	
Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.	Related Products: <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Cable Type = Spec 55 • Cable Style = Jacketed, Round-Braid Shielded <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Voltage Rating (VAC) = 600 <p>Dimensions:</p> <ul style="list-style-type: none"> • Conductor Outer Diameter (mm [in]) = 2.20 [0.087] • Shield (Screen) Diameter (mm [in]) = 3.28 [0.129] <p>Body Features:</p> <ul style="list-style-type: none"> • Wire Size (AWG/CM) = 12 AWG • Cable Jacket Color = White • Conductor Type = Tin-Plated Copper • Wire Color = White • Nominal Outside Diameter (mm [in]) = 3.68 [0.145] • Wire Diameter (mm [in]) = 2.82 [0.111] <p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Conductors = 1 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • Government/Industry Qualification = Yes • Government/Industry Part Number = M27500-12SD1T23 • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Range (°C) = -65 - +150 • Wire Size - Details = 12 AWG 2.98 mm², 0.0046 in², 37 x 28 AWG <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Airframe - Medium Weight <p>Packaging Features:</p> <ul style="list-style-type: none"> • Wire Source = United States <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem

Feedback

<p>Corporate Information</p> <ul style="list-style-type: none"> About TE Investors News Room Supplier Portal Careers Terms & Conditions Privacy Policy AODA Accessibility Policy AODA Multi-Year Accessibility Plan 	<p>Quick Links</p> <ul style="list-style-type: none"> Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center Site Map 	<p>Customer Support</p> <ul style="list-style-type: none"> Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account 	<p>Keep Me Informed</p>
---	---	--	--------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A1811-12-9-9CS2275](#)