


TSB23005DS Product Details

 **Live Product Chat**



TSB23005DS
(9-1437387-1)

TE Internal Number: 9-1437387-1



Superseded

[Search for Replacement Parts](#)

Europa Terminal Blocks

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- Terminal Block
- 8.00 mm Centerline
- Number of Circuits = 5
- Wire Range = 0.12-3.00; [26-12] mm [AWG]
- With Wire Protection

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Terminal Block
- [Number of Circuits](#) = 5
- [Integrated Fuse](#) = No
- Color = Natural
- Screw Size = M3 Screw
- Screw Material = Steel
- CSA File No. = LR28387
- UL Recognized = File No. E60677

Mechanical Attachment:

- Screw Plating = Bright Zinc/Chrome

Electrical Characteristics:

- Current Rating (Amps.) = 30
- Voltage Rating (VAC) = 250
- Wire Protector Material = Stainless Steel

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 8.00 [0.315]
- [Wire Range \(mm \[AWG\]\)](#) = 0.12-3.00; [26-12]
- [Wire Protection](#) = With
- [Ground](#) = Without
- [Series](#) = TSB230
- Flammability Rating = UL 94V-2

Contact Related Features:

- Contact Base Material = Brass
- Contact Mating Area Plating Material = Tin

Housing Related Features:

- Housing Material = Polyamide

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- [Temperature Range \(?C\)](#) = 105

Other:

- Brand = Buchanan

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TSB23005DS](#)