










.033 .027 [0.84 0.69	.208 .168 [5.28 4.27	.040 .020 [1.02 0.51	.544 [13.82 .524 [13.31	.2188 [55.58 .2168 [55.07	.248 .238 [6.30 6.05	.439 .419 [11.15 10.64	.620 [15.75 .590 [14.99	.428 [10.87 .418 [10.62	2.411 [61.24 2.401 [60.99	2.069 [52.55 2.059 [52.30	2.650 [67.31 2.620 [66.55	MS18277-1	50	5	M24308/23-11F	443976-5	1-443976-0							
			.282 [57.96 .262 [57.45	.2505 [63.63 2.495 [63.37			2.164 [54.97 2.154 [54.71	2.744 [69.70 2.714 [68.94	MS18276-1	37	4	M24308/23-10F	443976-4	443976-9										
			.432 [10.97 .412 [10.46	1.635 [41.53 1.615 [41.02			1.857 [47.17 1.847 [46.91	1.516 [38.51 1.506 [38.25	2.103 [53.42 2.073 [52.65	MS18275-1	25	3	M24308/23-9F	443976-3	443976-8									
			1.093 [27.76 1.073 [27.25	1.317 [33.45 1.307 [33.20			.976 [24.79 .966 [24.54	1.556 [39.52 1.526 [38.76	MS18274-1	15	2	M24308/23-8F	443976-2	443976-7										
			.769 [19.53 .749 [19.02	.989 [25.12 .979 [24.87			.648 [16.46 .638 [16.21	1.228 [31.19 1.198 [30.43	MS18273-1	9	1	M24308/23-7F	443976-1	443976-6										
			.544 [13.82 .524 [13.31	.2188 [55.58 .2168 [55.07			.248 .238 [6.30 6.05	.439 .419 [11.15 10.64	.620 [15.75 .590 [14.99	.428 [10.87 .418 [10.62	2.411 [61.24 2.401 [60.99	2.069 [52.55 2.059 [52.30	2.650 [67.31 2.620 [66.55	MS18277-1	50	5	M24308/23-11F	443976-5	443976-5					
			.282 [57.96 .262 [57.45	.2505 [63.63 2.495 [63.37					2.164 [54.97 2.154 [54.71	2.744 [69.70 2.714 [68.94	MS18276-1	37	4	M24308/23-10F	443976-4	443976-4								
			.432 [10.97 .412 [10.46	1.635 [41.53 1.615 [41.02					1.857 [47.17 1.847 [46.91	1.516 [38.51 1.506 [38.25	2.103 [53.42 2.073 [52.65	MS18275-1	25	3	M24308/23-9F	443976-3	443976-3							
			1.093 [27.76 1.073 [27.25	1.317 [33.45 1.307 [33.20					.976 [24.79 .966 [24.54	1.556 [39.52 1.526 [38.76	MS18274-1	15	2	M24308/23-8F	443976-2	443976-2								
			.769 [19.53 .749 [19.02	.989 [25.12 .979 [24.87					.648 [16.46 .638 [16.21	1.228 [31.19 1.198 [30.43	MS18273-1	9	1	M24308/23-7F	443976-1	443976-1								
			N	M					L	J	H	G	F	E	D	C	B	A	INSERT ARRANGEMENT	NO OF POS	SHELL SIZE	MILITARY P/N ON CONNECTOR		P/N ON CONNECTOR

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN GWR	J.A.BAKER	05MAY97			TE Connectivity		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD	NAME	AMPLITUDE RECEPTACLE ASSY W/ SIZE 20 SHELLED PC BOARD CONTACTS SERIES 109, POSTED SLOTS 1 THRU 5			
		0 .PLC ± -- 1 .PLC ± -- 2 .PLC ± -- 3 .PLC ± -- 4 .PLC ± -- ANGLES				PRODUCT SPEC					
MATERIAL		FINISH				APPLICATION SPEC	SIZE	GAGE CODE	DRAWING NO	RESTRICTED TO	
-		-				WEIGHT	A1	00779	C=443976		
CUSTOMER DRAWING							SCALE	4:1	SHEET	1 OF 2	REV D



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M24308/23-8F](#)