


| REVISIONS |     |                                                              |          |          |
|-----------|-----|--------------------------------------------------------------|----------|----------|
| ZONE      | REV | DESCRIPTION                                                  | DATE     | APPROVED |
| ALL       | A   | REDRAWN                                                      | 05/04/12 |          |
|           | B   | ADDED 4UX10HP P/N : 5241310-07                               | 04/06/16 |          |
|           | C   | ADDED 6UX6HP P/N : 5261306-07<br>AND 3UX6HP P/N : 5231306-07 | 09/16/16 |          |



| ASSY PART NO | DESCRIPTION | HEIGHT "H" | WIDTH "W" | CENTER "C" | LEFT MOUNTING HOLE "LMHE" | RIGHT MOUNTING HOLE "RMHE" | PLACES "N" |
|--------------|-------------|------------|-----------|------------|---------------------------|----------------------------|------------|
| 5231304-07   | 3U X 4HP    | 5.060      | 0.788     | 4.823      | 0.294                     | -                          | 2          |
| 5231306-07   | 3U X 6HP    | 5.060      | 1.188     | 4.823      | 0.294                     | 0.294                      | 4          |
| 5231308-07   | 3U X 8HP    | 5.060      | 1.588     | 4.823      | 0.294                     | 0.294                      | 4          |
| 5231312-07   | 3U X 12HP   | 5.060      | 2.388     | 4.823      | 0.294                     | 0.294                      | 4          |
| 5231342-07   | 3U X 42HP   | 5.060      | 8.388     | 4.823      | 0.294                     | 0.294                      | 4          |
|              |             |            |           |            |                           |                            |            |
| 5241310-07   | 4U X 10HP   | 6.810      | 1.988     | 6.573      | 0.294                     | 0.294                      | 4          |
|              |             |            |           |            |                           |                            |            |
| 5261304-07   | 6U X 4HP    | 10.310     | 0.788     | 10.073     | 0.294                     | -                          | 2          |
| 5261306-07   | 6U X 6HP    | 10.310     | 1.188     | 10.073     | 0.294                     | -                          | 2          |
| 5261308-07   | 6U X 8HP    | 10.310     | 1.588     | 10.073     | 0.294                     | 0.294                      | 4          |
| 5261312-07   | 6U X 12HP   | 10.310     | 2.388     | 10.073     | 0.294                     | 0.294                      | 4          |
| 5261324-07   | 6U X 24HP   | 10.310     | 4.788     | 10.073     | 0.294                     | 0.294                      | 4          |
|              |             |            |           |            |                           |                            |            |
| 5291304-07   | 9U X 4HP    | 15.560     | 0.788     | 15.323     | 0.294                     | -                          | 2          |
| 5291308-07   | 9U X 8HP    | 15.560     | 1.588     | 15.323     | 0.294                     | 0.294                      | 4          |
| 5291312-07   | 9U X 12HP   | 15.560     | 2.388     | 15.323     | 0.294                     | 0.294                      | 4          |



- |                                                                        |  |                        |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
|------------------------------------------------------------------------|--|------------------------|--|---------------------------------------------------------------------------------------|--|------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------|--|
| UNLESS OTHERWISE SPECIFIED                                             |  | APPROVALS              |  | NAME                                                                                  |  | DATE       |  |  11115 VANOWEN ST.,<br>NORTH HOLLYWOOD,<br>CA 91605<br>ELECTRONICS & TECHNOLOGY, INC. www.vectorelect.com |  |              |  |
| DIMENSIONS ARE IN INCHES                                               |  | DRAWN                  |  | TRUSHAR                                                                               |  | 05/04/12   |  | <div>3U, 6U, 9U NON EMC</div> <div>FILLER PANEL</div>                                                                                                                                          |  |              |  |
| TOLERANCES:                                                            |  | CHECKED                |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| DEC X.X ±0.1                                                           |  | ENGINEER               |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| DEC X.XX ±0.03                                                         |  | QA                     |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| DEC X.XXX ±0.010                                                       |  |                        |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| FRACTIONS ±0.050                                                       |  |                        |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| ANGLES ±1°                                                             |  |                        |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| GD & T : ASME Y14.5-2009                                               |  |                        |  |                                                                                       |  |            |  |                                                                                                                                                                                                |  |              |  |
| MATERIAL <span style="border: 1px solid black; padding: 2px;">2</span> |  | THIRD ANGLE PROJECTION |  |  |  | SIZE       |  | DWG. NO.                                                                                                                                                                                       |  | REV          |  |
| FINISH <span style="border: 1px solid black; padding: 2px;">4</span>   |  |                        |  |                                                                                       |  | D          |  | 52RU304-HP                                                                                                                                                                                     |  | C            |  |
|                                                                        |  |                        |  |                                                                                       |  | SCALE: 2:1 |  | CAGE CODE: 82893                                                                                                                                                                               |  | SHEET 1 OF 1 |  |

NOTES : UNLESS OTHERWISE SPECIFIED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vector:

[5291304-07](#) [5261304-07](#) [5261308-07](#) [5231312-07](#) [5231304-07](#) [5231308-07](#)