

### Data Sheet

#### Handheld RF Counters/Detectors with Bargraph Power Meter

B&K Precision's new models 103, 104 & 106 are compact, pocket sized Frequency Counters with signal strength meters. They are ideal for radio measurement, security and test applications. These small counters are unique because they offer the ability to see the strength of the signal via the digital bargraph just below the frequency displayed on the LCD. Rechargeable batteries and antenna are included.

- 16 Section bargraph to show RF strength
- 300MHz direct counter with 0.1Hz resolution (except model 106)
- 4 Selectable gate speeds (except model 106)
- 10 Digit LCD (7 digit model 106)
- Display hold
- Rechargeable NiCd battery pack included
- Low battery indicator



#### Model 103

1MHz - 3GHz Handheld Frequency/ Strength Meter

- Compact size
- Low cost

■ **IMPORTANT:** this unit only works with Analog Signals



#### Model 104

10Hz - 3GHz Deluxe Handheld Frequency Counter/ Strength Meter

- Measures frequency or period
- Filter helps prevent display of random noise

■ **IMPORTANT:** this unit only works with Analog Signals



#### Model 106

Smart RF Counter 30MHz - 2.8GHz

- Frequency counter for digital, on/off keying and analog signals (>250µs pulse width)
- Squelch adjustment for input signals
- Low power consumption (5 hours approx. battery life)



### B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887  
Tel: 714-921-9095, Fax: 714-921-6422  
[www.bkprecision.com](http://www.bkprecision.com)

Specifications subject to change without notice

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[105](#)