

Video Monitor Tester



1280A



Features

models

	1280A	1275
Color Bars	✓	✓
Black Raster	✓	✓
Color Rasters	✓	✓
Window	✓	✓
Dot	✓	✓
Crosshatch	✓	✓
Multiple Outputs	✓	✓
RGB	✓	✓
H/HV Sync	✓	✓
V Sync	✓	✓
Auto/Manual	✓	✓
Gray scale	✓	✓
Available Patterns	✓	✓
PC: 1280 x 1024	✓	✓
1024 x 768 (non-interlaced)	✓	✓
841 5A (interlaced)	✓	✓
SVGA 800 x 600	✓	✓
SVGA 1024 x 768	✓	✓
VGA 640 x 480	✓	✓
VGA 640 x 350	✓	✓
VGA 720 x 400	✓	✓
EGA	✓	✓
CGA	✓	✓
MDA	✓	✓
Mac: 1280 x 1024	✓	✓
1152 x 870	✓	✓
1024 x 768 (non-interlaced)	✓	✓
832 x 624	✓	✓
640 x 480	✓	✓
512 x 384	✓	✓
Power Source	9V battery or AC adapter	
Dimensions	3.125 x 9.44 x 9.25" (78 x 240 x 235mm)	1.5 x 3.8 x 5.7" (38 x 97 x 145mm)
Weight	2.5lbs. (1.1kg)	0.5 lbs. (227g)

Accessories

One Year Warranty

SUPPLIED:	BE-12 AC adapter	9V battery
OPTIONAL:		BE-12 AC adapter



1275

Model 1280A

The 1280A is a fully featured bench-top design to test both Mac and PC monitors. All patterns can be manually selected or place the 1280A in Auto for automatic cycling of each available pattern. Designed to test (burn-in) one to four monitors, the 1280A can also be used as a display generator. Full color, green, blue, red, black and white.

■ PC and Mac Patterns

■ 16 Monitor Types/Resolution Selections

■ Color bar, Cross Hatch, Dot, Raster, Windows® selection

■ VGA, SVGA, RGB, HV, V & Four DB-15 (Rear panel) for multiple monitor burn-in

Model 1275

Great handheld unit to test PC and Mac monitors. The model 1275 is ideal for the field or the service bench. Small, portable and very effective, the 1275 generates crosshatch, dots, color bars and raster patterns in green, blue, red, black and white.

■ CGA, VGA, SVGA

■ Standard DB-9, DB-15 and DB-15 Hi-res mini connectors



BK PRECISION®

For your nearest distributor, call 800-462-9832 or www.bkprecision.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1280A](#)