

SPECIFICATIONS

1502

Description: 1.5V/3V/4.5V/6V/9V/12V 0.5A Power Supply
Input Voltage: 115VAC 60Hz
Environment Temperature: 25C°

	MIN.	TYP.	MAX.	UNIT
Output Voltage 1.5V	1.3		1.8	V
Output Voltage 3V	2.6		3.4	V
Output Voltage 4.5V	4.2		3.4	V
Output Voltage 6V	5.5		6.4	V
Output Voltage 9V	8.5		9.4	V
Output Voltage 12V	11.5		12.5	V
Output Current		0.5		A
Voltage Regulation:				
Load (0-100% Load)			120	mV
Line (110-130VAC Variation)			300	mV
Ripple & Noise			200	mVp-p
No Load Input Current			80	mA
Full Load Input Current (All Rated Load)			180	mA
Fuse 1		2		A
Fuse 2		0.5		A

Dimensions (W X D X H): 4.33 x 5.51 x 3.27"

Weight: 2.43 lbs.

Operation:

Plug model 1502 into AC outlet. Turn power switch on, power light will come on.
Adjust control knob to desired voltage.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1502](#)