

SPECIFICATION

1513

Description: 3.3/4.5/6/7.5/9/12VDC, 1Amps
Switching Mode Power Supply Power supply
AC Input: 120VAC 60Hz
Environment Temperature: 25C°

	MIN.	TYP.	MAX.	UNIT
Rated Output 3.3V	3.1	3.3	3.6	V
Rated Output 4.5V	4.3	4.5	4.9	V
Rated Output 6V	5.8	6	6.4	V
Rated Output 7.5V	7.3	7.5	7.9	V
Rated Output 9V	8.8	9	9.4	V
Rated Output 12V	11.8	12	12.4	V
Output Current		1		A
Voltage Regulation:				
Load (0-100%)			300	mV
Line (+- 10% variation)			60	mV
Ripple & Noise (peak to peak)			100	mVp-p
No Load Input Current			60	mA
Full Load Input Current			300	mA
Insulation Resistance (500VDC)	100			M?
Withstanding Test (10mA, 60s)	2.3			KV
Efficiency (@ 12V, 1A)	75	79		%

Operation:

Plug model 1513 into AC outlet. Turn power switch on, power light will come on. Adjust control knob to desired voltage.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1513](#)