

Data Sheet

Single Output Isolation Transformer
Model 1604A



The 1604A (single output) isolation transformer provides the necessary safety factor for servicing any transformerless AC powered equipment.

Specifications	1604A
Isolation	leakage less than 0.1 mA
Output Voltage (typical)	117-129 V nominal (120 V input)
Output Current	1.25 A continuous (2 A intermittent)
Power Requirements	120 VAC, 60 Hz, 175 W
Operating Temperature	32 to 104 °F (0 to +40 °C)
Dimensions (HxWxD)	4" x 4" x 5.5" (100 x 100 x 140 mm)
Weight	6 lbs (2.7 kg)
One-Year Warranty	
Included Accessories	Instruction manual & power cord

Features & Benefits

- Leakage: less than 0.1 mA
- Output Voltage: 117 to 129 V (120 V input)
- Output Current: 1.25 A continuous

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1604A](#)