

Data Sheet

DC Regulated Power Supplies

Model 1665, 1666, 1667

- Over voltage protection, short circuit temperature
- Constant voltage operation
- Constant current operations
- Presetting current limiting value



Model 1666

Specifications	Models		
	1665	1666	1667
Output Voltage:	1-20VDC	1-40VDC	1-60VDC
Output Current:	0-10A	0-5A	0-3.3A
Ripple & Noise:	20mV	20mV	20mV
Load Regulation:	0.5%+200mV	0.5%+100mV	0.5%+100mV
Line Regulation:	20mV	20mV	20mV
Input Voltage:	90-265VAC, 50/60Hz		
Meter Type:	3 1/2 Digital LED		
Meter Accuracy:	1%+2 counts		
Dimension (HxWxD):	4.5" x 8" x 10.8"		
Weight:	6.6 lbs		

B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

B&K Precision:

[1666](#) [1667](#) [1665](#) [1666-NIST](#)