

Data Sheet

BK Precision offers a wide variety of current clamp meters for safe non-invasive current measurement. The new line of mini clamp meters are practical where a traditional sized meter may be too cumbersome to use. Both models 312B and 313A feature autoranging capabilities and are ideal for use in cramped quarters. The BK Precision mini clamps are more than just current clamps they offer the ability to measure voltage and resistance. Both the 312B and 313A meet CE requirements and come with a one year warranty.

- Low cost
- Autoranging
- Data Hold Function
- 2 times/sec Sample Rate
- Clamp Opening Size 25mm
- Low Power Indicator

Model 313A

	Range	Resolution	Accuracy
AC Current	600A	100mA	2% ± 10 dgt
DC Current	600A	100mA	2.5% ± 10 dgt
AC Voltage	600V	100mV	1.5% ± 5 dgt
DC Voltage	600V	100mV	1% ± 3 dgt
Resistance	1000 Ω	0.1 Ω	1% ± 3 dgt

Model 312B

	Range	Resolution	Accuracy
AC Current	200A	100mA	2% ± 5 dgt
	600A	1A	2% ± 5 dgt
AC Voltage	200V	100mV	1.5% ± 5 dgt
	600V	100mV	
Resistance	200 Ω	0.1 Ω	1.9% ± 3 dgt



B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[313A](#)