

BK Precision offers a wide variety of current clamp meters for safe non-invasive current measurement. The new milli-amp clamp meters are practical where a traditional sized meter may be to cumbersome to use. Model 316 features autoranging capabilities and is ideal for use in cramped quarters. The BK Precision milli-amp clamp meter is more than just current clamps it offers the ability to measure voltage and resistance. It also has the added functions of Peak Hold, Data Hold, and has a 4 digit display, these are an invaluable tool when evaluation or repairing electronic equipment. The model 316 meets CE requirements and come with a one year warranty.

- Low Cost
- Pocket Size
- 4 digit Display
- Auto Power Off
- 1mA Resolution
- Autoranging
- Peak Hold Function
- Data Hold Function
- Touch Zero Function
- Analog Signal Function



	Range	Resolution	Accuracy
AC Current:	10A	1mA	2% ±10dgt
	80A	10mA	
	80-100A	10mA	3.5% ±10dgt
DC Current:	10A	1mA	2.5% ±10dgt
	80A	10mA	
	80-100A	10mA	4.5% ±10dgt
AC Voltage:	600V	100mV	1.5% ±5dgt
DC Voltage:	600V	100mV	1% ±2dgt
Resistance:	10KΩ	1Ω	1% ±3dgt

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

B&K Precision:

[316](#) [316-NIST](#) [316-NIST-W/DATA](#)