

SPECIFICATIONS

1505

DESCRIPTION 0-20VDC, 500mA Power Supply
INPUT VOLTAGE 115VAC, 60Hz
ENVIRONMENTAL TEMPERATURE: 25°C

0-20VDC:	Min.	Max
Minimum Output Voltage Range	0.1V	20V
Maximum Output Voltage	20.5V	22V
Output Current	500mA,typical	
VOLTAGE REGULATION:		
Load (0-100% load)		200mV
Line (100-130VAC Variation)		100mV
Ripple & Noise		100mVp-p
No Load Input current		60mA
Full Load Input Current (20V, 500mA)		180mA
Fuse	0.5A	

Dimensions (W X D X H): 141 mm x 80 mm x 68 mm

Weight: 0.90 kgs

Description:

This power supply has a current limiter that protects the circuitry and the output b automatically returns to normal after an overload.

Operation:

Plug model 1505 into AC outlet. Turn power switch on, power light will come on. Adjust control knob to desired voltage.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1505](#)