







DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°



P.C.B. LAYOUT



NO.	H	H1	H2
DT002-S11BBB-1	10.70	10.25	8.80

HATCHED AREA SHOW SOLDERING LAND

SPECIFICATION:

- 1.RATING: 30VDC, 0.1A.
- 2.CONTACT RESISTANCE: 1Ω MAX.
- 3.INSULATION RESISTANCE: 100VDC-100MΩ MIN.
- 4.WITHSTAND VOLTAGE: 100VAC-1 MINUTE
- 5.OPERATING FORCE: 35gf MAX.
- 6.LIFE CYCLE: 50,000 CYCLE

DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION	DATE	APPROVAL	DESIGN	UNIT	MODE	DETECT SWITCH
2011/02/20	KAVEN		8.3 -> 8.8	2010/10/27	KAVEN	SCALE	mm	1 : 1	DT002-S11BBB
					ALAN	VIEW		2D FILE NAME	DT002-S11BBB
					XUWEI	VER.	01	3D FILE NAME	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[DT002-S11BBB](#)