




DIMENSION		TOLERANCE
BELOW 10 mm		± 0.3
10~100 mm		± 0.5
ABOVE 100 mm		± 0.8
ANGLE		± 3°

SCHEMATIC



P.C.B. LAYOUT



1. LOCK TYPE.
2. RATING : 30 V DC , 1 A.
3. CONTACT RESISTANCE : 50 mΩ MAX .
4. INSULATION RESISTANCE : 500 V DC , 100 MΩ MIN .
5. OPERATING FORCE : 450±150 gf
6. OPERATING TEMPERATURE : -20°C ~ 70°C .
7. OPERATING LIFE : 10,000 CYCLES .

△	DATE	UNIT	MODE	M SERIES MINI PUSH BUTTON SWITCH
△	APPROVAL	SCALE	PART	M-B2PL-17
△	CONFIRM	VIEW	2D FILE NAME	M-B2PL-17
DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION	DESIGN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[M-B2PL-17](#)