





DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°



CIRCUIT DIAGRAM


LED SCHEMATIC

P.C.B. LAYOUT



SPECIFICATION

- 1P1T
- RATING : 100mA 12V DC
- CONTACT RESISTANCE : 200 mΩ MAX.
- INSULATION RESISTANCE : 500 V DC , 100 MΩ MIN.
- OPERATING FORCE : 200 ± 80gf
- MECHANICAL LIFE : 1,000,000
- OPERATING TEMPERATURE : -20°C ~ 70°C



△				DATA	2011/4/06	UNIT	mm	MODE	PUSH SWITCH WITH LED
△				APPROVAL	KAVEN	SCALE	1 : 1	PART	PS011A SERIES
△				CONFIRM	ALAN	VIEW	2D FILE NAME	PS011A-N11TBB-NRGB	
DATA	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION						
				DESIGN	vansun	VER.	01	3D FILE NAME	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[PS011A-N11TBB-NRGB](#)