



DIMENSION	TOLERANCE
BELOW 10 mm	± 0.1
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°

### CIRCUIT DIAGRAM



### P.C.B LAYOUT



### COLOR OF LED

G	Green	Y	Yellow
R	Red	B	Blue
O	ORANGE	W	White
X	Without		


### Housing Color


G	Gray
K	Black
X	Without

### CAP Color

G	Gray	N	Green
R	Red	Y	Yellow
K	Black	X	Without

1. RATING : 12 V DC , 50 mA .
2. CONTACT RESISTANCE : 100 mΩ MAX .
3. INSULATION RESISTANCE : 500 V DC , 100mΩ MIN .
4. OPERATION FORCE : 180±50 gf .
5. OPERATION TEMPERATURE RANGE : -20°C ~ +70°C .
6. OPERATION LIFE : 500,000 CYCLES .



△1				DATE	2008/05/13	UNIT	mm	MODE	TACT SWITCH	<div>WB Well Buying Industrial Co.,Ltd.</div>				
△2				APPROVAL	KA VEN	SCALE	1 : 1	PART	TC002-N11AX1XXUBXX					
△1				CONFIRM	ALAN	VIEW		2D FILE NAME	TC002-N11AX1XXUBXX					
	DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION				DESIGN	ZCJ		VER.	01	3D FILE NAME	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Well Buying:

TC002-N11AX1XXUBXX