



DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°

CIRCUIT DIAGRAM






P.C.B.MOUNTING HOLE



CAP COLOR

W	WHITE
K	BLACK
R	RED
B	BULE
X	WITHOUT

- SPECIFICATION :**
1. RATING : 20 VDC ; 1mA .
 2. CONTACT RESISTANCE : 200 Ω MAX .
 3. INSULATION RESISTANCE : 100 V DC - 100 M Ω MIN .
 4. WITHSTAND VOLTAGE : 250 V AC - 1 MINUTE .
 5. OPERATING FORCE : 125 ± 35 gf .
 6. LIFE CYCLE : 300,000 CYCLE .



△				DATE	2012/3/5	UNIT	mm	MODE	TACT SWITCH
△				APPROVAL	KAVEN	SCALE	1 : 1	PART	TC011-AS2AWXXUGUY
△				CONFIRM	ALAN	VIEW		2D FILE NAME	TC011-AS2AWXXUGUY
DATA	APPROVAL	DESIGN		ENGINEERING CHANGE DESCRIPTION					
				DESIGN	HQ	VER.	01	3D FILE NAME	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[TC011-AS2AWXXUGUY](#)