


DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10~100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°


SPECIFICATION :

1. RATING : 12 VDC,50mA .
2. CONTACT RESISTANCE : 100mΩ MAX , .
- 3.INSULATION RESISTANCE:100mΩ MIN 500 V DC .
4. BREAKDOWN VOLTAGE : 230 VDC .
5. OPERATING FORCE : 250±50gf .
- 6.TOTAL TRAVEL : 0.35±0.1mm .
7. OPERATING TEMPERATURE: -20°C ~ 70°C .
8. LIFE CYCLE : 100,000 CYCLE .


P.C.B. LAYOUT



CIRCUIT DIAGRAM



(ULTRA GREEN)

△				DATA	2010/11/18	UNIT	mm	MODE	TACT SWITCH	<div>WB Well Buying Industrial Co.,Ltd.</div>			
△				APPROVAL	KAVEN	SCALE	1 : 1	PART	TC012N11AS3W1UGXX				
△				CONFIRM	ALAN	VIEW		2D FILE NAME	TC012N11AS3W1UGXX				
	DATA	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION				DO	VER.		01	3D FILE NAME	
				DESIGN	DQ	VER.							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Well Buying:

TC012-N11AS3WTUGXX