

Wiha Industrial SoftGrip Pliers & Cutters

Made by Wiha

Maximum comfort in daily use, smooth operation & optimum force transmission without uncomfortable pressure points. Natural brushed finish.



New dynamic joint provides 40% easier cuts & significantly longer tool life

Induction hardened cutters

Ergonomic shape for maximum user comfort



Slip guards molded into grip

Anti-slip soft dual material handles for safe gripping

40/60 Dynamic Joint



Industrial SoftGrip Combination Pliers



SHOP

309 Industrial Combination Pliers DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping and holding as well as cutting soft and hard wires and cables. Two component Industrial SoftGrip ergonomic handles.

Item No.	mm	Inch	Cutting Capacity AWG	Pkg.	lbs.
30901	160	6.3	#10	1	.52
30903	180	7.0	#9	1	.67
30905	200	8.0	#8	1	.83

Industrial SoftGrip Heavy Duty Combo Pliers



SHOP

309 Industrial Heavy Duty Combination Pliers DIN ISO 5746

Larger Head and extra long cutting edges for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping & holding as well as cutting wires & cables ranging in hardness from soft to extremely hard. Two component SoftGrip ergo handles.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30907	200	8.0	#7	1	.81
30909	225	9.0	#6	1	1.02

Industrial SoftGrip Linemans Crimpers



SHOP

30912 Industrial Linemans Crimpers DIN ISO 5746

Extra large head and extra long cutting edges for flat and round cables. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping & holding as well as cutting wires & cables ranging in hardness from soft to extremely hard. Two component SoftGrip ergo handles.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30912	225	9.0	#4	1	1.05

Industrial SoftGrip Stripping Pliers



SHOP

30947 Industrial Stripping Pliers DIN ISO 5743

Heavy duty forged with induction hardened cutting edges for even stripping of insulation. Easy to use adjustment screw allows stripping diameter to be quickly changed. Return spring for effortless use. Special C70 tool steel edges. Stripping Diameter: .019" to .393".

Item No.	mm	Inch	Stripping Capacity Copper AWG	Pkg.	lbs.
30947	160	6.3	#8 - #28	1	.48

For stripping up to Ø 5mm/#4 AWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wiha:](#)

[30901](#) [30903](#) [30905](#) [30907](#) [30909](#) [30912](#) [30947](#)