



A TableSource Table Box installed in a typical work surface application.

Table Boxes bring technology to the point-of-use

Table Boxes bring technology into the user's work area. Routing of power, communications and A/V connectivity to the work surface needs to be unobtrusive with maximum accessibility and flexibility.

Our wide range of table box solutions offer the flexibility to meet the connectivity and power configurations requirements needed to run business smoothly, while enhancing the overall room appearance. From desks to lab benches, table boxes make technology easily accessible to the user.

Features & Benefits

- **Range of solutions.** Table Boxes allow you to access services on, above or below the work surface with cord-ended or field-wired options. Standard off-the-shelf, field configurable or custom configurations are available to meet any work area need.
- **Variety of applications.** Office workstations, conference rooms, even home offices can increase productivity by bringing access to connections up to the work surface.
- **Safety.** Wiremold Table Boxes meet U.S. and Canadian safety standards.
- **Aesthetics.** Elegant yet functional access to services includes cover style and color options to meet room décor. Built-in cable management with easy to install and replaceable retractors for communications and USB cables keeps the work surface clear.
- **Ease of installation.** From clamping to the edge of a desk or table, or using the supplied template to create the cut out, Wiremold Table Boxes are made easy to install so you can get back to business.

Compliance

TableSource™ Table Boxes:

Cord-Ended TableSource Boxes : cULus Listed Relocatable Power Tap: File E66421 Guide XBYS
Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.

Hard-Wired TableSource Boxes: cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.

deQuorum™ Flip-Up Table Boxes:

Cord-Ended deQuorum Table Boxes (DQFP): cULus Listed Relocatable Power Tap: File E66421 Guide XBYS
Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.

Hard-Wired deQuorum Table Boxes (DQFF): cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.






Desktop Power Center Slim:

cETLus Listed Furniture Power Distribution Unit Listed to US & Canadian Safety Standards.

Desktop Power Center with Surge:

cETLus Listed Furniture Power Distribution Unit Listed to US & Canadian Safety Standards.

Table Boxes Quick Selection Guide

TABLE BOX MODEL	SVC. LOCATION @ TABLE	CORD LENGTH	FIELD WIRED OPTION	COVER COLOR/MATERIAL	ELECTRICAL OUTLETS	USB POWER RATING	DATA OPENINGS
TableSource Table Boxes (Standard Model) 	Above	6'	Yes	Clear Anodized Aluminum	(1) 15A Duplex, USB	2.4A	2 Openings with Adapters for Ortronics® Series II, TracJack or Wiremold Open System devices
TableSource Table Boxes (Configurable Model) 	Above	2'-12'	Yes	Clear Anodized Aluminum	(1-4) 15A Duplexes Gasketed, USB	2.4A	1-4 Openings with Adapters for Ortronics® Series II, TracJack or Wiremold Open System devices
deQuorum Flip Up Table Boxes 	Flush	6'	Yes	Black, Stainless	(1) 15A or 20A Duplex, (1) USB Duplex Receptacle	3.1A	Adapters for Ortronics® Series II, TracJack or Wiremold Open System devices
Desktop Power Center Slim 	Above	6'	No	Matte Black or Gloss White with Gray Face	(2-3) 15A Outlets with (2) USB Charging Outlets	3.1A	N/A
Desktop Power Center w/Surge 	Above	6'	No	Black with Magnesium Side Panels	(3) 15A Outlets with (2) USB Charging Outlets	2.1A	N/A

* Extron® Electronics MAAP modules are sold separately.

TableSource™ Table Boxes

TableSource™ Table Boxes provide effortless work surface accessibility for power and communication. They are offered in a range of standard or custom configured product. TableSource Table Boxes can be easily added to any work area and require minimal, adaptable installation.

CODE REFERENCE

Cord-Ended TableSource: cULus Listed Relocatable Power Tap:
 File E66421 Guide XBY5

Hard-Wired TableSource: cULus Listed Multioutlet Assembly:
 File E15191 Guide PVGT

Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.

TABLESOURCE TABLE BOXES COLOR OPTIONS


Standard TableSource Table Boxes are available in a clear anodized aluminum finish. Other finishes are available for configurable units. Consult the configurator located on the next page.



TableSource™ Table Boxes provide flexibility in décor, datacom connectivity options, and installation to meet specific functional and aesthetic needs.

TableSource Table Boxes Ordering Information


TableSource Activations in this chart are packaged with a mounting clip that attaches to the work surface and a hardware bag of adapters that allows the communication openings to accept either Ortronics Series II, TracJack or Wiremold Open System.



CATALOG NUMBER	FINISH	UNIT LENGTH		15A DUPLEX	CORD LENGTH		COMM. OPENINGS
		INCHES	(MM)		FEET	(MM)	
TSAX1F0AL1U	Clear Anodized	13"	(330.2mm)	1	6'	(1.83m)	0
TSAX1F1AL1U	Clear Anodized	15 1/2"	(393.7mm)	1	6'	(1.83m)	1
TSAX1F2AL1U	Clear Anodized	18 5/32"	(461.2mm)	1	6'	(1.83m)	2

Country of Origin:US

TableSource Activations in this chart are packaged with a mounting clip that attaches to the work surface and a hardware bag of adapters that allows the communication openings to accept either Ortronics Series II, TracJack or Wiremold Open System.



CATALOG NUMBER	FINISH	UNIT LENGTH		15A DUPLEX	CORD LENGTH		COMM. OPENINGS
		INCHES	(MM)		FEET	(MM)	
TSAM1F0AL1U	Clear Anodized	13"	(330.2mm)	1	6'	(1.83m)	0
TSAM1F1AL1U	Clear Anodized	15 1/2"	(393.7mm)	1	6'	(1.83m)	1
TSAM1F2AL1U	Clear Anodized	18 3/32"	(461.2mm)	1	6'	(1.83m)	2

Country of Origin:US

TableSource™ Table Boxes Configurator

Design a Cord-Ended TableSource Table Box

Sample Part: **TSAM2H1IV2U**

IMPORTANT

Use this chart to configure your own custom TableSource activation. Many of the configurations are standard offerings, and can be quoted and delivered to you quickly with the help of our Wiremold Customs group. Just call in with your TableSource part number, and they will be able to supply you with a quote, technical specifications and a CAD Drawing.

1. Select face for mounting device. Input letter.

A Face

B Face

2. Do you want optional mounting bracket for backslash application?

Mounting Clip X

Backslash Bracket M

3. Number of Duplexes (from 1-4). Input number.

4. Choose a length and input the corresponding letter for that length.

Length Feet [metric]	Code Letter
2 [0.6m]	B
3 [0.9m]	C
4 [1.2m]	D
5 [1.5m]	E
6 [1.8m]	F
7 [2.1m]	G
8 [2.4m]	H
9 [2.7m]	I
10 [3.0m]	J
11 [3.4m]	K
12 [3.7m]	L

NOTE: Cord color is black.

5. Choose number of Communication Adapters (from 1-4). Input number.

6. Choose color of activation and devices. Input two-letter color code.

WH- Painted White with black devices

BK- Painted Black with Black devices

IV- Painted Ivory with black devices

AL- Anodized Aluminum with gray devices

7. Choose number of USB modules. Input a number followed by "U"

#U = Number of USB Modules

Data Cables egress out the back (the side opposite the devices).

NOTE: Wiremold Open System, Ortronics Series II and TracJack modules provided with all assemblies.

Design a Hard-Wired TableSource Table Box

Sample Part: **TSAP2Z1BK2UG**

IMPORTANT

Use this chart to configure your own custom TableSource activation. Many of the configurations are standard offerings, and can be quoted and delivered to you quickly with the help of our Wiremold Customs group. Just call in with your TableSource part number, and they will be able to supply you with a quote, technical specifications and a CAD Drawing.

1. Select face for mounting device. Input letter.

A Face

B Face

2. Mounting Styles

T - Mounting Ears

P - Mounting Stud

3. Number of duplexes (from 1-4). Input number.

4. Choose face for 6' [1.8m], three-wire whip to exit. Y STYLE

Z STYLE

5. Choose number of communication adapters (from 1-4). Input number.

6. Choose color of activation and devices. Input two-letter color code.

WH- Painted White with black devices

BK- Painted Black with Black devices

IV- Painted Ivory with black devices

AL- Anodized Aluminum with gray devices

7. Choose number of USB modules. Input a number followed by "U"

#U = Number of USB Modules

8. Choose if Deadfront GFCI Protection is needed. If not, leave blank.

G = Dead Front GFCI Module

Data Cables egress out the back (the side opposite the devices).

NOTE: Wiremold Open System, Ortronics Series II and TracJack modules provided with all assemblies.

deQuorum™ Flip-Up Table Boxes

deQuorum™ Flip-Up Table Boxes provide flexibility in décor, communication connectivity options, and installation to meet specific functional and aesthetic needs. Flip-Up Table Boxes bring the modules above the work surface when in use for easy access.

CODE REFERENCE

DQFP Table Boxes:
cULus Listed Relocatable Power Tap: File E66421 Guide XBY5

DQFF Table Boxes:
cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Listed to US & Canadian Safety Standards. Meets Article 380 of NEC.

deQUORUM FLIP-UP TABLE BOXES COLOR OPTIONS

deQuorum Flip-Up Table Box Covers are available in the following finishes: Black and Stainless.



deQuorum™ Flip-Up Table Boxes provide flexibility in décor, communication connectivity options, and installation to meet specific functional and aesthetic needs.

deQuorum Flip-Up Table Box Part Number Configurator

deQuorum Flip-Up Table Boxes

D Q F

deQuorum Series:

DQF = deQuorum
Flip-Up

Wiring Option:

P = Cord Ended
F = Field Wired

Receptacle Amperage:

15 = 15A
20 = 20A

USB:

U = USB

Unit Color:

BK = Black
ST = Stainless


Second Gang:

Communications = 2A
One Gang Only= Leave Blank

NOTE: Part Number Configurator can be used both to identify stock product configurations and also to request custom configurations from the factory. Consult the factory for more information.

deQuorum Flip-Up Table Boxes Ordering Information


DQFP15BK DQFP15ST



Single Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle. Unit comes with a 6' (1.83m) cord. Available in black or stainless finishes.

Country of Origin: Mexico


DQFP15UBK DQFP15UST



Single Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Available in black or stainless finishes.

Country of Origin: Mexico


DQFP15BK-2A DQFP15ST-2A



Dual Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle. Second opening will accept adapter for one (1) Wiremold CM Series Open System 2A module, one (1) Ortronics Series II or one (1) TracJack adapter to accommodate a wide range of communication outlets. Adapters are included in hardware bag. Unit comes with a 6' (1.83m) cord. Available in black or stainless finishes.

Country of Origin: Mexico

DQFP15UBK-2A DQFP15UST-2A




Dual Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Second opening will accept adapter for one (1) Wiremold CM Series Open System 2A module, one (1) Ortronics Series II or one (1) TracJack adapter to accommodate a wide range of communication outlets. Adapters are included in hardware bag. Unit comes with a 6' (1.83m) cord. Available in black or stainless finishes.

Country of Origin: Mexico

NOTE: Single-gang table boxes require a cutout of 4 1/8" x 5" (105mm x 127mm).
Double-gang table boxes require a cutout of 4 1/8" x 10 1/4" (105mm x 260mm).

deQuorum Flip-Up Table Boxes Ordering Information


DQFF15BK DQFF15ST



Single Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle. Unit can be field-wired with MC or EMT using any 1/2" trade size connector. Hot, neutral and ground wires come with quick connectors for activation. Available in black or stainless finishes.

Country of Origin: Mexico


DQFF15UBK DQFF15UST



Single Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit can be field-wired with MC or EMT using any 1/2" trade size connector. Hot, neutral, and ground wires come with quick connects for activation. Available in black or stainless finishes.

Country of Origin: Mexico


DQFF20BK DQFF20ST



Single Flip-Up Unit – Unit includes one (1) 20A black tamper-resistant duplex receptacle. Unit can be field-wired with MC or EMT using any 1/2" trade size connector. Hot, neutral and ground wires come with quick connectors for activation. Available in black or stainless finishes.

Country of Origin: Mexico

DQFF20UBK DQFF20UST



Single Flip-Up Unit – Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit can be field-wired with MC or EMT using any 1/2" trade size connector. Hot, neutral, and ground wires come with quick connects for activation. Available in black or stainless finishes.

Country of Origin: Mexico

NOTE: Single-gang table boxes require a cutout of 4 1/8" x 5" (105mm x 127mm).

Desktop Power Center Solutions

Desktop Power Center Slim uses a modern aesthetic to bring power and smart USB charging to the work surface. It's compact design and multiple mounting methods free up desk space and help to remove clutter.

CODE REFERENCE

cETLus Listed Furniture Power Distribution Box
Listed to US & Canadian Safety Standards.

DESKTOP POWER CENTER SLIM COLOR OPTIONS

Desktop Power Center Slim is available in matte black or gloss white with a gray face.




Desktop Power Center Slim puts smart USB charging where you need it.

Desktop Power Center Slim Ordering Information

WSPC220BK WSPC220WH

Two Outlet Unit – Unit Includes two (2) 15A tamper-resistant power receptacles and two (2) smart USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Includes screw in mounting plate for forward facing outlets. Available in matte black (WSPC220BK) or gloss white (WSPC220WH) with a gray face.


Country of Origin: China




WSPC320BK WSPC320WH

Three Outlet Unit – Unit Includes three (3) 15A tamper-resistant power receptacles and two (2) smart USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Includes screw in mounting plate for forward facing outlets. Available in matte black (WSPC320BK) or gloss white (WSPC320WH) with a gray face.


Country of Origin: China



WSPCBKTBK WSPCBKTGY



Clamp



Right Angle Screw-In
Mounting Plate

Alternate Mounting Kit – Kit includes clamp for screwless mounting, and right angle screw in mounting plate. The two piece clamp allows the Desktop Power Center Slim to be installed against partition walls without dismantling them. The clamp allows the outlets to be mounted forward or upward facing. The right angle screw in mounting plate allows the outlets to be mounted facing upward. Available in black or gray finishes.

Country of Origin: China



Desktop Power Center Solutions

Desktop Power Center with Surge brings surge-protected power and USB charging outlets up to the work surface by utilizing existing cord drop openings in office desks and table tops or by mounting onto the edge of a desk or table top.

CODE REFERENCE

cETLus Listed Furniture Power Distribution Box
Listed to US & Canadian Safety Standards.

DESKTOP POWER CENTER W/SURGE COLOR OPTIONS

Desktop Power Center w/ Surge is available in black with magnesium side panels.



Desktop Power Center with Surge provides easy access to surge-protected power and USB services.

Desktop Power Center with Surge Ordering Information

WSC320-S

USB Desktop Power Center – Has three (3) surge-protected 15A power outlets, two (2) USB charging outlets and a 6' [1.83m] cord. Units come with accessories for mounting into round cutouts in desk or edge mounting on desks or other work surfaces. Ships in corrugated box.

Country of Origin: China




WSC320-S Desktop Power Center with mounting components




Desktop Power Center with Surge Mounting Options


Installs through an existing cord drop opening.



Back View



Installs on the edge of a work surface.



Vertical Markets

- | | | | |
|---------------|-------------|-----------------|-----------|
| • Commercial | • Education | • Entertainment | • Retail |
| • Hospitality | • Parks | • Healthcare | • Transit |

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



NOTE: The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiremold:

[TSAM1F0AL1U](#) [TSAM1F0BK1U](#) [TSAM1F1AL1U](#) [TSAM1F1BK1U](#) [TSAM1F2AL1U](#) [TSAM1F2BK1U](#) [TSAX1F0AL1U](#)
[TSAX1F0BK1U](#) [TSAX1F1AL1U](#) [TSAX1F1BK1U](#) [TSAX1F2AL1U](#) [TSAX1F2BK1U](#)