




Wiremold
RC7 Furniture Feed Poke-Thru Assembly, Black
Part No. RC7AFFTCBK



Complete with one-piece finish flange and conduit assembly with one 3/4inch and two 1/2inch trade size conduit adapters and closure plugs. Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC7AFFTC Series Poke-Thru Devices require a 3 1/16inch (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

Complete with one-piece finish flange and conduit assembly with one 3/4inch and two 1/2inch trade size conduit adapters and closure plugs.

Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS).

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC7AFFTC Series Poke-Thru Devices require a 3 1/16inch (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564132011	Country Of Origin	Mexico
Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] & 314 of NEC	Type	Poke-Thru

Dimensions

Product Width US	7.0 in	Product Weight US	4.72 lb
Product Volume US	808.5 cu in	Product Depth US	16.5 in

Product Height US	7.0 in	Cubic Capacity	24.5 in³
Core Hole Size	3.063 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Buy American Act Compliance			
NAFTA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Number of Outlets	0		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wiremold:](#)

[RC7AFFTCBK](#)