




Wiremold
RC7AFFTC Multi-Service Poke-Thru Flush Furniture Feed Poke-Thru Assembly
Part No. RC7AFFTCBS



Complete with one-piece finish flange and conduit assembly with one 3/4" and two 1/2" trade size conduit adapters and closure plugs. Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC7AFFTC Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

Complete with one-piece finish flange and conduit assembly with one 3/4" and two 1/2" trade size conduit adapters and closure plugs	Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS)
NOTE: Assembled with scrub water gasket	For use on tile or carpet floors
RC7AFFTC Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole	Floor covering thickness 1/8" minimum
Floor covering thickness 1/8" minimum	

Specifications

General Info

Product Line	Wiremold	UPC Number	786564132028
Country Of Origin	Mexico	Construction	Assembled
Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] & 314 of NEC	Type	Poke-Thru

Dimensions

Product Height US	16.5 in	Cubic Capacity	24.5 in³
-------------------	---------	----------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Cable Entry	Knockouts
-------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wiremold:](#)

[RC7AFFTCBS](#)