



Capacitor value 1000 pF

Technical Characteristics

Materials:

Insulator: Thermoplastic UL94 V-0 black
 Contact: Copper alloy
 Contact finish: 0,2u Au over nickel
 Shell: steel tin plated

Characteristics:

Working voltage: 100 V
 Current rating: 5A
 Contact resistance: max. 10 MOHM
 Insulation resistance: > 1 GOHM
 Temperature range: -55° - 125°C

General tolerances				
tolerances	± 0,1	± 0,2	± 0,2	± 0,3
size (mm)	> 0,5 up to 3	> 3 up to 6	> 6 up to 30	> 30 up to 120

				Date	Name	DESCRIPTION				
				Drawn	12-07-24	Jelisarow	DSubFilter			
				Checked			D-Sub Filter Adapter_15 pol._1000 pF			
						Scale	1:1	Position		SIZE
				Würth Elektronik eiSos GmbH & Co KG D-74638 Waldenburg Max-Eyth-Straße 1		Drawing.- No. 232016003				A4
REV	FILE	DATE	BY	EDV NO	232016003.dft		System :Solid Edge V20			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[232016003](#)