

## 915 MHz Antenna



### Key Features

- 915 MHz
- ¼ Lambda Dipole Antenna
- SMA/m connector

### Description

The Hydra is a robust antenna for 915 MHz applications. The antenna has a SMA/m connector. With its high efficiency > 70% it is well suited for every application with critical range.

Because of the antenna technology, the dipole design, no additional ground plane is required.

### Range of Application

The environmental robustness of IP65 and operating temperature of -40°C to 85°C makes the Hydra a good match for industrial applications. The Hydra suits as well for all 915 MHz applications like ISM, IoT, M2M and many more.

### Specification

Part number	2600130083
Frequency	915 MHz (868 to 928 MHz)
VSWR	< 2.5
Gain	max. 0.9 dBi
Height	179 mm
Diameter	10 mm
Weight	14.3g
Connector	SMA male
Temperature	-40 to +80°C
Impedance	50 Ohms
Efficiency	70%
IP Ingress Protection	65

### Ordering Information

Item no.	Description
2600130083	Antenna 915 MHz



#### Würth Elektronik eiSos GmbH & Co.KG

Phone +49 7942 945 0

Email [wireless-sales@we-online.com](mailto:wireless-sales@we-online.com)

Internet [www.we-online.com](http://www.we-online.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[2600130083](#)