



RECOMMENDED PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT MATERIAL: COPPER ALLOY
CONTACT PLATING: TIN
CONTACT TYPE: STAMPED

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 115°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 8A
WORKING VOLTAGE: 300VAC
WITHSTANDING VOLTAGE: 1.6KV
CONTACT RESISTANCE: 20 mOhm max


STANDARD
ULus CERTIFIED E315414

PITCH: 3.81 MM

SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
BOX

DIMENSION
A = 3.81 x (NB PINS -1) +2.8
B = 3.81 x (NB PINS -1)
C = (3.81 x NB PINS) +0.79

RoHS Compliant					PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		DESCRIPTION: SERIE 3073 - 3.81 MM REVERSED PCB VERTICAL	SIZE A4
G									
F									
E									
D									
C					APPROVAL: FBr	UNIT: MM	WERI PART NO: 691 307 300 0xx		
B						SCALE:			
A	11-JUN-15	PDF	AK			SHEET: 1/2			
REV	DATE	FILE	BY			DRAW: AK			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691307300004](#)