




N=Number of contacts



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT: BRASS
WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 20A
WORKING VOLTAGE: 300VAC
WITHSTANDING VOLTAGE: 1.6KV
CONTACT RESISTANCE: 20 mOhm max

STANDARD
cULus CERTIFIED E315414 / MODEL NUMBER 3074

MECHANICAL
PITCH: 7.62MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3074

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			DESCRIPTION: SERIE 3074 - 7.62MM REVERSED GENDER VERTICAL PCB HEADER WR-TBL WERI PART NO: 691 307 400 0xx	SIZE A4
G									
F									
E									
D									
C	05-OCT-10	CURRENT RATING	JC	APPROVAL: RJ	UNIT: MM				
B	16-OCT-09	STANDARD	JP		SCALE:				
A	05-NOV-08	PDF	JP		SHEET: 1/1				
REV	DATE	FILE	BY		DRAW: MARVIN				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691307400008](#)