




N=Number of contacts



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT: BRASS
WIRE GUARD: PhBz TIN PLATED

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 20A
WORKING VOLTAGE: 300VAC
WITHSTANDING VOLTAGE: 1.6KV
CONTACT RESISTANCE: 20 mOhm max


STANDARD
cULus CERTIFIED E315414 / MODEL NUMBER 3074

MECHANICAL
PITCH: 7.62MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3074

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		DESCRIPTION: SERIE 3074 - 7.62MM REVERSED GENDER VERTCAL PCB HEADER WR-TBL WERI PART NO: 691 307 400 0xx	SIZE A4
G								
F								
E								
D				APPROVAL: RJ	UNIT: MM			
C	05-OCT-10	CURRENT RATING	JC					
B	16-OCT-09	STANDARD	JP					
A	05-NOV-08	PDF	JP					
REV	DATE	FILE	BY		DRAW: MARVIN			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691307400003](#)