




N=Number of contacts



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PA 66

FLAMABILITY RATING: UL94-V0

COLOR: GREEN

CONTACT: BRASS

SOLDER TAIL PLATING: TIN

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C

COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 20A

WORKING VOLTAGE: 300VAC

WITHSTANDING VOLTAGE: 1.6KV

CONTACT RESISTANCE: 20 mOhm max

STANDARD

UL CERTIFIED E315414 / MODEL NUMBER 3075

MECHANICAL

PITCH: 5.08MM


SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3075

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = ± 0.2

.XX = ± 0.15



APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/1

DRAW: MARVIN

DESCRIPTION: SERIE 3075 - 5.08MM REVERSED GENDER VERTICAL PCB
HEADER WR-TBL

WERI PART NO: 691 307 500 0xx

SIZE

A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691307500008](#)