




TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PA 66
 FLAMABILITY RATING: UL94-V0
 COLOR: GREEN
 CONTACT: BRASS
 SOLDER TAIL PLATING: TIN

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 20A
 WORKING VOLTAGE: 300VAC
 WITHSTANDING VOLTAGE: 1.6KV
 CONTACT RESISTANCE: 20 mOhm max


STANDARD
 ULus CERTIFIED E315414 / MODEL NUMBER 3095

MECHANICAL
 PITCH: 5.08MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3095

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK				
G						APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 3095 - 5.08MM REVERSED GENDER HORIZONTAL PCB HEADER WR-TBL		SIZE A4
F							SCALE:			
E							SHEET: 1/1	WERI PART NO: 691 309 510 0xx		
D	17-JAN-12	REFERENCE	GG	DRAW: MARVIN						
C	05-OCT-10	CURRENT RATING	JC							
B	13-OCT-09	STANDARD	JP							
A	04-NOV-08	PDF	JP							
REV	DATE	FILE	BY							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691309510005](#)