




TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBT
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT: BRASS
SOLDER TAIL PLATING: TIN

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 20A
WORKING VOLTAGE: 300VAC
WITHSTANDING VOLTAGE: 1.6KV
CONTACT RESISTANCE: 20 mOhm max


STANDARD
cULus CERTIFIED E315414 / MODEL NUMBER 3114

MECHANICAL
PITCH: 7.62MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3114

RoHS Compliant									
G				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15		 WÜRTH ELEKTRONIK		
F									
E									
D									
C				APPROVAL: RJ	UNIT: MM		DESCRIPTION: SERIE 3114 - 7.62MM OPEN VERTICAL PCB HEADER WR-TBL		SIZE A4
B	14-OCT-09	STANDARD	JP		SCALE:				
A	12-NOV-08	PDF	JP		SHEET: 1/1		WERI PART NO: 691 311 400 0xx		
REV	DATE	FILE	BY		DRAW: MARVIN				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691311400012](#)