







N = Number of contacts



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBT
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT: BRASS
SOLDER TAIL PLATING: TIN

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL	cULus	VDE
CURRENT RATING:	20A	20A
WORKING VOLTAGE:	300VAC	300VAC
WITHSTANDING VOLTAGE:	1.6KV	2.5KV
CONTACT RESISTANCE: □	20 mOhm max	


MECHANICAL
PITCH: 5.00MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3117

CERTIFICATION



RoHS Compliant					PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15				D
G										
F										
E										
D										
C				APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 3117 - 5.00MM CLOSE VERTICAL PCB HEADER WR-TBL		SIZE		
B					SCALE:					
A	04-NOV-08	PDF	JP		SHEET: 1/1	WERI PART NO: 691 311 700 1xx				
REV	DATE	FILE	BY		DRAW: MARVIN					
								A4		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691311700105](#)