




PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT: BRASS
SOLDER TAIL PLATING: TIN
FLANGES SCREW NUT: BRASS M2.5

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL	cULus	VDE
CURRENT RATING:	10A	10.5A
WORKING VOLTAGE:	300VAC	300VAC
WITHSTANDING VOLTAGE:	1.6KV	2.5KV
CONTACT RESISTANCE:	20 mOhm max	


MECHANICAL
PITCH: 3.81MM


SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

SERIE 3233

CERTIFICATION



RoHS Compliant					PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			
G									
F									
E									
D									
C				APPROVAL: RJ	UNIT: MM	DESCRIPTION: SERIE 3233 - 3.81MM VERTICAL PCB HEADER WITH FLANGES			SIZE
B					SCALE:				
A	31-OCT-08	PDF	JP		SHEET: 1/1	WERI PART NO: 691 323 300 0xx			
REV	DATE	FILE	BY		DRAW: MARVIN				
								A4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691323300006](#)