




TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMMABILITY RATING: UL94-V0
COLOR: GREEN
METAL HOUSING: BRASS (CuZn)
TERMINAL SCREW: STEEL ZINC PLATING
TERMINAL SCREW SLOT TYPE: "-"
WIRE GUARD: PhBz TIN PLATED
FLANGES SCREW: STEEL M2.5

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 20 A
WORKING VOLTAGE: 300 VAC
WITHSTANDING VOLTAGE: 1.6 KV
CONTACT RESISTANCE: 20 mOhm max


STANDARD
cULus CERTIFIED E315414

MECHANICAL
SOLID WIRE: 24-12 AWG / 0.205-3.31 MM²
STRANDED WIRE: 24-12 AWG / 0.205-3.31 MM²
TORQUE: 5.0 Lb-In / 0.56 Nm

WIRE STRIPE LENGTH: 7-8 MM
SCREW: M3.0
PITCH: 7.62 MM

PACKAGING
BOX

DIMENSION
A = (NB. PINS - 1) x PITCH
B = (NB. PINS x PITCH) - 2

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		DESCRIPTION: SERIE 3404 - 7.62MM VERTICAL CABLE ENTRY PLUG WITH FLANGES - WR-TBL	SIZE A4
G								
F								
E								
D	12-MAY-16	DRAWING	AK	APPROVAL: FBr	UNIT: MM SCALE: SHEET: 1/2 DRAW: MARVIN	WERI PART NO: 691 340 400 0xx		
C	21-OCT-09	SCREW	JP					
B	14-OCT-09	STANDARD	JP					
A	05-NOV-08	PDF	JP					
REV	DATE	FILE	BY					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691340400003](#)