





1				2				3				4				5																																																																																																																															
																																																																TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PA 66 FLAMMABILITY RATING: UL94-V0 COLOR: GREEN METAL HOUSING: BRASS (CuZn) TERMINAL SCREW: STEEL ZINC PLATING TERMINAL SCREW SLOT TYPE: "-" WIRE GUARD: PhBz TIN PLATED FLANGES SCREW: STEEL M2.5 ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO 105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL cULus CURRENT RATING: 20 A WORKING VOLTAGE: 300 VAC WITHSTANDING VOLTAGE: 1.6 KV CONTACT RESISTANCE: 20 mOhm max STANDARD  CERTIFIED E315414 MECHANICAL SOLID WIRE: 24-12 AWG / 0.205-3.31 MM² STRANDED WIRE: 24-12 AWG / 0.205-3.31 MM² TORQUE: 5.0 Lb-In / 0.56 Nm WIRE STRIPE LENGTH: 7-8 MM SCREW: M3.0 PITCH: 7.62 MM PACKAGING BOX DIMENSION A = (NB. PINS -1) x PITCH B = (NB. PINS x PITCH) -2																A																																																															
																																																																																B																																																															
																																																																																																																C																															
RoHS Compliant																PROJECTION:																GENERAL TOLERANCE																																																																																																															
G																																.X = +/- 0.2																																																																																																															
F																																.XX = +/- 0.15																																																																																																															
E																																																																																																																																															
D																12-MAY-16																DRAWING																AK																																																																																															
C																21-OCT-09																SCREW																JP																APPROVAL: FBr																UNIT: MM																DESCRIPTION: SERIE 3404 - 7.62MM VERTICAL CABLE ENTRY PLUG WITH FLANGES - WR-TBL																SIZE																															
B																14-OCT-09																STANDARD																JP																																SCALE:																																																															
A																05-NOV-08																PDF																JP																																SHEET: 1/2																WERI PART NO: 691 340 400 0xx																																															
REV																DATE																FILE																BY																																DRAW: MARVIN																																																A4															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691340400005](#)