





1				2				3				4				5																																			
   																TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PA 66 FLAMMABILITY RATING: UL94-V0 COLOR: GREEN METAL HOUSING: BRASS (CuZn) TERMINAL SCREW: STEEL ZINC PLATING TERMINAL SCREW SLOT TYPE: "-" WIRE GUARD: PhBz TIN PLATED FLANGES SCREW: STEEL M2.5 ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO 105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL cULus CURRENT RATING: 20 A WORKING VOLTAGE: 300 VAC WITHSTANDING VOLTAGE: 1.6 KV CONTACT RESISTANCE: 20 mOhm max STANDARD  CERTIFIED E315414 MECHANICAL SOLID WIRE: 24-12 AWG / 0.205-3.31 MM² STRANDED WIRE: 24-12 AWG / 0.205-3.31 MM² TORQUE: 5.0 Lb-In / 0.56 Nm WIRE STRIPE LENGTH: 7-8 MM SCREW: M3.0 PITCH: 7.62 MM PACKAGING BOX DIMENSION A = (NB. PINS -1) x PITCH B = (NB. PINS x PITCH) -2				A																															
B																																																			
C																																																			
D																																																			
<table><tr><th colspan="4">RoHS Compliant</th></tr><tr><td>G</td><td></td><td></td><td></td></tr><tr><td>F</td><td></td><td></td><td></td></tr><tr><td>E</td><td></td><td></td><td></td></tr><tr><td>D</td><td>12-MAY-16</td><td>DRAWING</td><td>AK</td></tr><tr><td>C</td><td>21-OCT-09</td><td>SCREW</td><td>JP</td></tr><tr><td>B</td><td>14-OCT-09</td><td>STANDARD</td><td>JP</td></tr><tr><td>A</td><td>05-NOV-08</td><td>PDF</td><td>JP</td></tr><tr><td>REV</td><td>DATE</td><td>FILE</td><td>BY</td></tr></table>				RoHS Compliant				G				F				E				D	12-MAY-16	DRAWING	AK	C	21-OCT-09	SCREW	JP	B	14-OCT-09	STANDARD	JP	A	05-NOV-08	PDF	JP	REV	DATE	FILE	BY	PROJECTION: 				GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15							
RoHS Compliant																																																			
G																																																			
F																																																			
E																																																			
D	12-MAY-16	DRAWING	AK																																																
C	21-OCT-09	SCREW	JP																																																
B	14-OCT-09	STANDARD	JP																																																
A	05-NOV-08	PDF	JP																																																
REV	DATE	FILE	BY																																																
				APPROVAL: FBr				UNIT: MM				DESCRIPTION: SERIE 3404 - 7.62MM VERTICAL CABLE ENTRY PLUG WITH FLANGES - WR-TBL				SIZE																																			
								SCALE:								A4																																			
								SHEET: 1/2				WERI PART NO: 691 340 400 0xx																																							
								DRAW: MARVIN																																											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691340400008](#)