





1	2	3	4	5																																					
			TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PA 66 FLAMABILITY RATING: UL94-V0 COLOR: GREEN CONTACT MATERIAL: COPPER ALLOY CONTACT TYPE: STAMPED CONTACT PLATING: TIN PLATED ENVIRONMENTAL OPERATING TEMPERATURE: -40°C UP TO +105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL CURRENT RATING: 12A WORKING VOLTAGE: 200V AC WITHSTANDING VOLTAGE: 1000 VAC/min CONTACT RESISTANCE: 20 mΩ max STANDARD  CERTIFIED E315414 SOLDERING JEDEC LEAD FREE WAVE SOLDERING PROCESS PACKAGING BOX																																						
		<table><tr><td>A</td><td>(N-1)X2.5</td></tr><tr><td>B</td><td>NX2.5+12.0</td></tr></table>	A	(N-1)X2.5	B	NX2.5+12.0																																			
A	(N-1)X2.5																																								
B	NX2.5+12.0																																								
																																									
<table><tr><td colspan="4">RoHS Compliant</td></tr><tr><td>G</td><td></td><td></td><td></td></tr><tr><td>F</td><td></td><td></td><td></td></tr><tr><td>E</td><td></td><td></td><td></td></tr><tr><td>D</td><td></td><td></td><td></td></tr><tr><td>C</td><td></td><td></td><td></td></tr><tr><td>B</td><td></td><td></td><td></td></tr><tr><td>A</td><td>24-JUL-14</td><td>PDF</td><td>AS</td></tr><tr><td>REV</td><td>DATE</td><td>FILE</td><td>BY</td></tr></table>					RoHS Compliant				G				F				E				D				C				B				A	24-JUL-14	PDF	AS	REV	DATE	FILE	BY	
RoHS Compliant																																									
G																																									
F																																									
E																																									
D																																									
C																																									
B																																									
A	24-JUL-14	PDF	AS																																						
REV	DATE	FILE	BY																																						
		PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15																																						
		APPROVAL: JC																																							
			UNIT: MM	DESCRIPTION: SERIE 382 - VERTICAL PCB HEADER WITH FLANGES -																																					
			SCALE:	PITCH 2.5 MM - WR-TBL																																					
			SHEET: 1/3	WERI PART NO: 691 382 030 0XX																																					
		DRAW: AS	SIZE A4																																						

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			
G								
F								
E								
D								
C			APPROVAL: JC	UNIT: MM	DESCRIPTION: SERIE 382 - VERTICAL PCB HEADER WITH FLANGES -		SIZE	
B				SCALE:				PITCH 2.5mm - WR-TBL
A	24-JUL-14	PDF		AS	SHEET: 2/3	WERI PART NO: 691 382 030 0XX		
REV	DATE	FILE		BY	DRAW: AS			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691382030002](#)