



PCB LAYOUT - COMPONENT VIEW

A	(N-1)X2.5
B	NX2.5+12.0

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA 66
FLAMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: TIN PLATED

ENVIRONMENTAL
OPERATING TEMPERATURE: -40°C UP TO +105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 12A
WORKING VOLTAGE: 200V AC
WITHSTANDING VOLTAGE: 1000 VAC/min
CONTACT RESISTANCE: 20 mΩ max

STANDARD
CERTIFIED E315414

SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
BOX

RoHS Compliant				PROJECTION:	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			D
G								
F								
E								
D				APPROVAL: JC	UNIT: MM	DESCRIPTION: SERIE 382 - VERTICAL PCB HEADER WITH FLANGES - PITCH 2.5 MM - WR-TBL		SIZE A4
C					SCALE:			
B					SHEET: 1/3	WERI PART NO: 691 382 030 0XX		
A	24-JUL-14	PDF	AS		DRAW: AS			
REV	DATE	FILE	BY					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691382030003](#)