





1	2	3	4	5				
				TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PA 66 FLAMABILITY RATING: UL94-V0 COLOR: GREEN CONTACT MATERIAL: COPPER ALLOY CONTACT TYPE: STAMPED CONTACT PLATING: TIN PLATED ENVIRONMENTAL OPERATING TEMPERATURE: -40°C UP TO +105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL CURRENT RATING: 12A WORKING VOLTAGE: 200V AC WITHSTANDING VOLTAGE: 1000 VAC/min CONTACT RESISTANCE: 20 mΩ max STANDARD  CERTIFIED E315414 SOLDERING JEDEC LEAD FREE WAVE SOLDERING PROCESS PACKAGING BOX				
		<table><tr><td>A</td><td>(N-1)X2.5</td></tr><tr><td>B</td><td>NX2.5+12.0</td></tr></table>		A	(N-1)X2.5	B	NX2.5+12.0	
A	(N-1)X2.5							
B	NX2.5+12.0							
								

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15		DESCRIPTION: SERIE 382 - VERTICAL PCB HEADER WITH FLANGES - PITCH 2.5 MM - WR-TBL WERI PART NO: 691 382 030 0XX	SIZE
G								
F								
E								
D								
C				APPROVAL: JC	UNIT: MM			
B					SCALE:			
A	24-JUL-14	PDF	AS		SHEET: 1/3			
REV	DATE	FILE	BY		DRAW: AS			

A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Würth Electronics:](#)

[691382030005](#) [691382030003](#) [691382030002](#) [691382030008](#) [691382030004](#) [691382030006](#)