





| | | | |
|---------------|-------------------|------|---------------|
| SOLDER SUFFIX | CUSTOMER TERMINAL | RoHS | LEAD(Pb)-FREE |
| LF1 | Sn96%, Ag4% | Yes | Yes |

more than you expect



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER | TEST CONDITIONS | VALUE |
|--------------------|-----------------------------------|----------------------|
| D.C. RESISTANCE | 3-1 @20°C | 0.062 ohms ±20% |
| D.C. RESISTANCE | 4-5 @20°C | 0.425 ohms ±20% |
| D.C. RESISTANCE | 8-6 @20°C | 0.006 ohms ±20% |
| D.C. RESISTANCE | 10-9 @20°C | 0.019 ohms ±20% |
| INDUCTANCE | 3-1 100kHz, 100mVAC, Ls | 37uH ±10% |
| LEAKAGE INDUCTANCE | 3-1 tie(6+8), 100kHz, 100mVAC, Ls | 3.5uH typ., 5uH max. |
| DIELECTRIC | 3-8 1500VDC, 1 second | - |
| DIELECTRIC | 3-10 1500VDC, 1 second | - |
| DIELECTRIC | 4-8 1500VDC, 1 second | - |
| DIELECTRIC | 4-10 1500VDC, 1 second | - |
| DIELECTRIC | 3-4 500VDC, 1 second | - |
| URNS RATIO | (3-1):(8-6) | 5.25:1, ±2% |
| URNS RATIO | (3-1):(10-6), tie(8+9) | 3.5:1, ±2% |
| URNS RATIO | (3-1):(4-5) | 1.91:1, ±2% |

DETAILS SUBJECT TO CHANGE

| | | | | | | |
|------|-------|--|--|--|-------------------------------------|---|
| REV. | DATE | Packaging Specifications Method: Tape & Reel PKG-0499 www.we-online.com/midcom | | Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13] | DRAWING TITLE TRANSFORMER | PART NO. 32395R-LF1 |
| 6C | 2/12 | | | | | |
| 6B | 10/07 | | | | | |
| 6A | 7/06 | SEE REVISION SHEET FOR REVISION LEVEL | | This drawing is dual dimensioned. Dimensions in brackets are in millimeters. | eiSos p/n: 750032395 | compliant RoHS SPECIFICATION SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750032395](#)