








Thickness=1.60mm

PC BOARD LAYOUT COMPONENT SIDE SHOWN

NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 35 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.
3. WAVE SOLDERING TEMPERATURE: 230°~250°(3~5 SECONDS)
4. RoHS COMPLIANT.

MATES WITH MODULAR PLUG CONFORMING TO  
FCC PART 68, SUBPART F.  
CUL FILE NO. E163191

| PART NUMBER    | GOLD PLATING | CONTACTS |
|----------------|--------------|----------|
| E5386-E00212-L | 6u"          | 6        |
| E5388-E00212-L | 6u"          | 8        |
| E5388-E00213-L | 15u"         | 8        |
| E5388-E00214-L | 30u"         | 8        |

DETACHED LISTS

MM (INCH)

0 ± 0.2  
.00 ± 0.15  
.000 ± 0.075

±  
±  
±

ANGLES ± 0.5

THIRD ANGLE PROJECTION

RoHS Compliant

DRTO Jief Chi

DATE 06/28/06

SCALE : 3 : 1

SHEET 1 OF 1

FULL RISE ELECTRONIC CO., LTD

TITLE 11.5 SIDE ENTRY 8P

FCC DEEP TYPE

DRAWING NO. CE533096-01

/PART NO. SEE NOTES

SIZE A3

REV 0

REV 0

REV 0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5388-E00212-L](#)