





NOTES:

ELECTRICAL:

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.
- LED RATINGS: FORWARD VOLTAGE: 2.2 VOLTS TYPICAL.
REVERSE VOLTAGE: 5 VOLTS MAXIMUM
- OPERATING: 750 CYCLES MIN.




MECHANICAL:

- HOUSING MATERIAL : PBT+30%G.F UL94V-0. COLOR-BLACK.
- INSERT MATERIAL : PBT+30%GF UL94V-0. COLOR-BLACK.
- BACK PLATE MATERIAL : PBT+30%GF. COLOR-BLACK.
- LED SIZE : 3.2*2.0*7.0*P=2.54mm.
- SHIELD MATERIAL : COPPER ALLOY 0.25mm THICKNESS PLATING NI.
- CONTACT MATERIAL : PHOSPHOR BRONZE 0.35mm THICKNESS OR 0.46mm.
- PLATING : GOLD PLATING OVER NICKEL.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

- STORAGE : -40°C TO +85°C.
 - OPERATION: 0°C TO 70°C.
 - WAVE SOLDERING TEMPERATURE: 230~250°C (5~10 SECONDS)
- MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68, SUBPART F.

CUL FILE No: E163191



PART NUMBER: E 5 J 8 8 - X X X X X X - L

- 1-LED1:GREEN ,LED2:YELLOW
 2-LED1:GREEN ,LED2:GREEN
 3-LED1:YELLOW ,LED2:GREEN
 4-LED1:G+Y ,LED2:G+Y
 5-LED1:RED ,LED2:GREEN
 7-LED1:YELLOW ,LED2:YELLOW
 D-LED1:G+R ,LED2:G+R
 E-LED1:GREEN ,LED2:RED
 N-LED1:GREEN ,LED2:G+Y
 P-LED1:Y+R ,LED2:GREEN
 Q-LED1:G+Y ,LED2:G+R
 S-LED1:Y+R ,LED2:Y+R
 V-LED1:Y+G ,LED2:Y+G
 K-LED1:G+Y ,LED2:GREEN

GREEN GREEN
 YELLOW YELLOW
 FOR P/N:E5J88-NXCOXX-L

GREEN GREEN
 YELLOW YELLOW
 FOR P/N:E5J88-KXCOXX-L

GREEN GREEN
 YELLOW YELLOW
 FOR P/N:E5J88-4XCOXX-L

GREEN GREEN
 RED YELLOW
 FOR P/N:E5J88-QXCOXX-L

GREEN GREEN
 RED RED
 FOR P/N:E5J88-DXCOXX-L

YELLOW YELLOW
 RED RED
 FOR P/N:E5J88-SXCOXX-L

GREEN YELLOW
 RED RED
 FOR P/N:E5J88-PXCOXX-L

YELLOW YELLOW
 GREEN GREEN
 FOR P/N:E5J88-VXCOXX-L

PLATING: 1-3u" 2-6u"
 3-15u" 4-30u" 5-50u"

- PLATE Tin SHIELD, STAMP PIN, LED LONG 7.00
- PLATE Ni SHIELD, STAMP PIN, LED LONG 7.00
- PLATE Tin SHIELD, ROUND PIN, LED LONG 7.00
- PLATE Ni SHIELD, ROUND PIN, LED LONG 7.00

0-W/O LOGO
 6-W/ FRE&UL

4-4 PORTS W/O MIDDLE POLE
 C-4 PORTS W/ MIDDLE POLE

0-NO SHIELD
 1-NO TAB 2-TOP TABS.
 3-SIDE TABS.
 4-TOP TABS & SIDE TABS.

MM (INCH)		DFTO PETERS	DATE 03/24/05	FULL RISE ELECTRONIC CO., LTD	
TOLERANCES EXCEPT AS NOTED		CHKD JAKE	DATE 2005/08/23		
		MFO	DATE		
		APPV LUSHENG	DATE 2005/08/23		
MM	±	MATERIAL :		TITLE	
.0 ± 0.20	±	QT'Y :		RJ45 SIDE ENTRY LED GANG JACK 4 PORTS	
.00 ± 0.15	±	FINISH :		DRAWING NO. GE5J3017-LC	
.000 ± 0.075	±	SCALE : 2:1		/PART NO. SEE NOTE	
ANGLES ±		DO NOT SCALE DRAWING		SIZE A3	
THIRD ANGLE PROJECTION		SHEET 1 OF 1		REV 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5J88-14LJD2-L](#) [E5J88-14LJP2-L](#) [E5J88-24LJ25-L](#) [E5J88-32HJ22-L](#) [E5J88-34C022-L](#) [E5J88-19LJP3-L](#) [E5J88-41LH24-LT](#)