

REVISION RECORD				
REV	ECHO	DESCRIPTION	DRFT	CHG
1		P/N ADD	Jako 05/25/04	
2		P/N ADD	Jako 06/17/04	
3		P/N ADD	PETERS 10/20/04	
4		ADD RIB	PETERS 10/25/04	
5		ADD RIB	PETERS 1/11/05	
6		DRAWING MODIFY	Jako 02/09/05	



Gold Thickness:
1- 3u" 2- 6u" 3-15u"
4-30u" 5-50u"
A-Plate Tin shield stamp pin
B-Plate Ni shield stamp pin
F-W/O TINNED GROUNDING TAB
0- W/O "FRE" LOGO
2- W/ "FRE" & "UL" LOGO
J- W/ 0 "FRE" LOGO. A05-0130

X4XXXX-L

Gold Thickness:
1- 3u" 2- 6u" 3-15u"
4- 30u" 5-50u"
A-Plate Tin shield stamp pin
B-Plate Ni shield stamp pin
F-W/O TINNED GROUNDING TAB
0- W/O "FRE" LOGO
2- W/ "FRE" & "UL" LOGO
J- W/ 0 "FRE" LOGO. A05-0130



PORTS	N	A±0.25	B±0.25	C±0.05
8	7	113.82	130.95	113.82
6	5	81.30	98.43	81.30
4	3	48.78	65.91	48.78
3	2	32.52	49.45	32.52
2	1	16.26	33.39	16.26

DETACHED LISTS			DFTO IRONDR	DATE 05/26/07							
	TOLERANCES EXCEPT AS NOTED		CHKD SAMMY	DATE 2005/2/19							
	<table><tr><td>MM</td><td>±</td></tr><tr><td>.0 ±0.20</td><td>±</td></tr><tr><td>.00 ±0.15</td><td>±</td></tr><tr><td>.000 ±0.075</td><td>±</td></tr></table>	MM	±	.0 ±0.20	±	.00 ±0.15	±	.000 ±0.075	±	APPLY/LUSHENG	DATE 2005/2/19
	MM	±									
	.0 ±0.20	±									
	.00 ±0.15	±									
	.000 ±0.075	±									
			MATERIAL :								
	ANGLES ±		QT'Y :								
			FINISH :								
THIRD ANGLE PROJECTION		SCALE : 3:2									

TITLE	RJ45 2*N LED JACK (STAMPED PIN)
-------	------------------------------------

DRAWING NO. GE5J3032		SIZE A3	REV 6 02/19
/PART NO. SEE NOTE			
DO NOT SCALE DRAWING		SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5J88-C4AJB2-L](#)