**NOTES:****ELECTRICAL:**


- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.
- LED RATINGS: FORWARD VOLTAGE: 2.2 VOLTS TYPICAL.  
REVERSE VOLTAGE: 5 VOLTS MAXIMUM
- OPERATING: 750 CYCLES MIN.

**MECHANICAL:**


- HOUSING MATERIAL : FR52 UL94V-0. COLOR-BLACK.
- INSERT MATERIAL : FR52 UL94V-0. COLOR-BLACK.
- BACK PLATE MATERIAL : FR52 COLOR-BLACK.
- LED SIZE : 3.2\*2.0\*7.0\*P=2.54mm.
- SHIELD MATERIAL : COPPER ALLOY 0.25mm THICKNESS PLATING NI.
- CONTACT MATERIAL : PHOSPHOR BRONZE 0.35mm THICKNESS .
- PLATING : GOLD PLATING OVER NICKEL.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.

**ENVIRONMENTAL:**

- STORAGE : -40°C TO +85°C.
  - OPERATION: 0°C TO 70°C.
  - WAVE SOLDERING TEMPERATURE: 255~265°C (5~10 SECONDS)
- MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68, SUBPART F. CUL FILE No:E163191



GREEN GREEN  
YELLOW YELLOW  
FOR P/N:E5J88-NXCOXX-L



GREEN GREEN  
YELLOW YELLOW  
FOR P/N:E5J88-4XCOXX-L

GREEN GREEN  
RED YELLOW  
FOR P/N:E5J88-QXCOXX-L

GREEN GREEN  
RED RED  
FOR P/N:E5J88-DXCOXX-L

YELLOW YELLOW  
RED RED  
FOR P/N:E5J88-SXCOXX-L

GREEN YELLOW  
RED RED  
FOR P/N:E5J88-PXCOXX-L

YELLOW YELLOW  
GREEN GREEN  
FOR P/N:E5J88-VXCOXX-L

PART NUMBER: E 5 J 8 8 - X X X J X -L

1-LED1:GREEN ,LED2:YELLOW  
2-LED1:GREEN ,LED2:GREEN  
3-LED1:YELLOW ,LED2:GREEN  
4-LED1:G+Y ,LED2:G+Y  
5-LED1:RED ,LED2:GREEN  
7-LED1:YELLOW ,LED2:YELLOW  
D-LED1:G+R ,LED2:G+R  
E-LED1:GREEN ,LED2:RED  
N-LED1:GREEN ,LED2:G+Y  
P-LED1:Y+R ,LED2:GREEN  
Q-LED1:G+Y ,LED2:G+R  
S-LED1:Y+R ,LED2:Y+R  
V-LED1:Y+G ,LED2:Y+G

PLATING: 1-3u" 2-6u"  
3-15u" 4-30u" 5-50u"

1- PLATE Tin SHIELD,STAMP PIN,LED LONG 7.00  
2- PLATE Ni SHIELD,STAMP PIN,LED LONG 7.00  
3- PLATE Tin SHIELD,ROUND PIN,LED LONG 7.00  
4- PLATE Ni SHIELD,ROUND PIN,LED LONG 7.00  
4-4 PORTS W/O MIDDLE POLE  
C-4 PORTS W/ MIDDLE POLE  
0-NO SHIELD  
1-NO TAB 2-TOP TABS.  
3-SIDE TABS.  
4-TOP TABS & SIDE TABS.

MM (INCH)		DFTO YANGLAN DATE 06/13/05		FULL RISE ELECTRONIC CO., LTD	
TOLERANCES EXCEPT AS NOTED		CHKD JAKE DATE 2005/08/10		TITLE	
		MFO DATE			
DETACHED LISTS		APPV LUSHENG DATE 2005/08/10		RJ45 SIDE ENTRY LED GANG JACK 4 PORTS	
MM		MATERIAL :		DRAWING NO. GE5J3128	
.0 ± 0.20		QT'Y :		/PART NO. SEE NOTE	
.00 ± 0.15		FINISH :		SIZE A3	
.000 ± 0.075		SCALE : 2:1		REV 1	
ANGLES ±		DO NOT SCALE DRAWING		SHEET 1 OF 1	
THIRD ANGLE PROJECTION					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5J88-34CJ23-L](#)